




**Part Number :** [638082310](#)

**Product Description :** FA2 Pneumatic Feed  
Applicator for MX150 Mat Seal/Unsealed Receptacle  
Terminals, 14 AWG, 16 AWG, 1.25mm<sup>2</sup> and 1.50mm<sup>2</sup>

**Series Number :** 207127

**Status :** Active

**Product Category :** Applicators and Crimp Modules



---

## Documents and Resources

### Tooling Specifications

[638082310-000.pdf](#)

[TM-638000029-001.pdf](#)

[638080200-000.pdf](#)

[638080200ES-000.pdf](#)

[638080200CN-000.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FA2 Pneumatic Feed Applicator for MX150 Mat Seal/Unsealed Receptacle Terminals, 14 AWG, 16 AWG, 1.25mm <sup>2</sup> and 1.50mm <sup>2</sup>
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FA2,MX150
Tool Type	Applicator
UPC	193264075553
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than

	Molex Tooling is used or where Molex Tooling is modified.
--	---

## Physical

Net Weight	1.000/g
------------	---------

## Applicable Parts

Description	Part Number
MX150 Female Terminal for Mat-Sealed Connectors, Gold Plating, 16-14 AWG, Left Reel Payoff	<u>330013003</u>
MX150 Female Terminal for Unsealed Connectors, Gold Plating, 16-14 AWG, Left Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330013021</u>
MX150 Female Terminal for Mat-Sealed Connectors, Silver Plating, 16-14 AWG, Left Reel Payoff	<u>330015001</u>
MX150 Female Terminal for Unsealed Connectors, Silver Plating, 16-14 AWG, Left Reel Payoff. Not suitable for MX150 Sealed Connectors.	<u>330015021</u>
MX150 Female Terminal for Mat-Sealed Connectors, Tin Plating, 16-14 AWG, Left Reel Payoff	<u>330123001</u>
MX150 Female Terminal for Unsealed Connectors, Tin Plating, 16-14 AWG, Left Reel Payoff. Not Suitable for MX150 Sealed Connectors.	<u>330123021</u>

This document was generated on Dec 16, 2025