

Product data sheet

Specifications



APC NetShelter SV, Server Rack Enclosure, 42U, 600W x 1200D mm, with Sides, Black

AR2500

Overview

Presentation	Deep Universal IT Enclosure for low to medium density server and networking applications that either require additional equipment clearance space or more open space for ease of access in the rear of the enclosure. Compact width to optimize data center space. 42U height to easily roll through doorways.
Lead time	Usually in Stock

Main

Product or component type	Rack enclosure
Number of rack unit	42U
Provided equipment	Baying hardware Doors Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters 4 x bolt down brackets Roof Side panels Unpacking sheet

Physical

Height	2057 mm
Width	600 mm
Depth	1200 mm
Net weight	121.3 kg
Colour	Black
Mounting preference	No preference
Mounting mode	Not rack-mountable
Mounting position	Vertical
Maximum mounting depth	916.9 mm
Minimum mounting depth	167.6 mm
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 18 gauge post 16 gauge rear door 19 gauge roof 18 gauge side panels
Permanent permissible load	459.9 kg dynamic 1000.2 kg static

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	218.1 cm
Package 1 Width	70 cm
Package 1 Length	130 cm
Package 1 Weight	139.706 kg

Contractual warranty


Warranty	5 year repair or replace
----------	--------------------------

Environmental Data


Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Total lifecycle Carbon footprint	424
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration

Use Again


 Repack and remanufacture	
Take-back	No

Image of product / Alternate images

Alternative



