



Part Number : [2033703346](#)
Product Description : QSFP-DD Cage Assembly, 1-by-4, PCI Fin Heat Sink, Spring Fingers, No Rear Legs, with Press-Fit Pins, Robust
Series Number : 203370
Status : Active
Product Category : High-Speed EMI Cages



Documents and Resources

Drawings

[2033703346 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2031430001-000.pdf](#)

[2031430001-PS.pdf](#)

[2031430005-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	High-Speed EMI Cages
Series	203370
Description	QSFP-DD Cage Assembly, 1-by-4, PCI Fin Heat Sink, Spring Fingers, No Rear Legs, with Press-Fit Pins, Robust
Application	Module-to-Board
Component Type	Cage Assembly
Product Name	QSFP-DD
UPC	193264257720

Electrical

Data Rate	112 Gbps (PAM-4), 56.0 Gbps
-----------	-----------------------------

Physical

EMI Panel / Bezel Mount	Spring Fingers
Light Pipes per Port	0
Material - Metal	Stainless Steel
Orientation	Horizontal
Packaging Type	Tray
Port Configuration	1x4

Rear Legs	0
Termination Interface Style	Through Hole - Compliant Pin
Thermal Height	PCI
Thermal Solutions	Fins

Mates With / Use With

Mates with Part(s)

Description	Part Number
QSFP-DD-to-QSFP-DD Passive Cable Assemblies, 56 Gbps	<u>201591</u>

Use with Part(s)

Description	Part Number
QSFP-DD Surface Mount Connectors	<u>202718</u>
QSFP-DD Surface Mount Connectors	<u>214733</u>

This document was generated on Dec 29, 2025