**Part Number :** 192150028
**Product Description :** VersaKrimp Butt Splice for 12-10 AWG Wire, Carton
**Series Number :** 19215
**Status :** Active
**Product Category :** Splices
**Engineering Part Number :** CS-346



## Documents and Resources

### Drawings

192150028_sd.pdf

### Specifications

PS-19902-013-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Splices |
| Series | 19215 |
| Description | VersaKrimp Butt Splice for 12-10 AWG Wire, Carton |
| Product Name | VersaKrimp |
| Style | Standard |
| Type | Butt Splice |
| UPC | 800755062533 |

### Agency

| | |
|---|---|
| CSA | LR18689 |
| UL | E32244 |

### Physical

| | |
|---|---|
| Barrel Type | Closed - Brazed |
| Insulation | None |
| Material - Metal | Copper |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 2.475/g |
| Packaging Type | Carton |
| Temperature Range - Operating | 149°C |
| Wire Size (AWG) | 10, 12 |
| Wire Size $mm^2$ | 3.30-5.00 |

### Solder Process Data

| | |
|---|---|
| Lead-Free Process Capability | N/A |

Downloaded from Arrow.com.

## Application Tooling

## Global

| Description | Part Number |
| --- | --- |
| PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm² - 0.5mm² | 640030100 |
| Crimp Head for the AT-200 Pneumatic Hand Tool | 640070100 |
| ServiceGrade Hand Crimp Tool - Ratchet | 640160038 |



Downloaded from Arrow.com.