

## USB 3.0 All-in-One Keystone/Panel Mount Angled Coupler (F/F), Black

MODEL NUMBER: U325-000-KPA-BK



Connects two USB-A cables to create one longer cable. Snaps into keystone cutout of a wallplate or panel. Or use the included panel mount adapter for installation in a motherboard, podium or kiosk.

### Description

The U325-000-KPA-BK USB 3.0 All-in-One Keystone/Panel Mount Angled Coupler connects two USB-A cables to create one longer connection, and its keystone design snaps easily into the cutout of a wallplate or panel. The angled connector makes the coupler easy to install in tight spaces. This coupler also comes with an optional panel mount adapter for securing the coupler to a podium or kiosk. Recommended for use with U325-Series USB A Male/Male cables, the U325-000-KPA-BK features molded nickel-plated connectors with gold-plated contacts for optimal signal transfer.

### Features

#### Strengthens Your USB 3.0 Connection

- Connects 2 USB-A cables for a longer cable run
- Recommended for use with U325-Series USB A Male/Male cables
- Keystone design for easy snap-in installation in wallplate or panel
- Includes panel mount adapter for installation in podium or kiosk
- Angled female connector for easy installation in tight spaces
- Molded nickel-plated connectors with gold-plated contacts for optimum signal transfer

### Specifications

OVERVIEW	
UPC Code	037332195647
Product Type	USB Keystone
Technology	USB 3.x
CONNECTIONS	

### Highlights

- Angled female connector for easy installation in tight spaces
- Gold-plated contacts for optimal signal transfer
- Panel mount adapter for securing to podium or kiosk
- Keystone design for snapping into standard wallplate
- Recommended for use with U325-Series USB A Male/Male cables

### Package Includes

- U325-000-KPA-BK USB All-in-One Keystone/Panel Mount Angled Coupler (F/F), Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Side A - Connector 1	USB 3.0 A (FEMALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / in.)	9.00 x 0.50 x 7.00
Shipping Dimensions (hwd / cm)	22.86 x 1.27 x 17.78
Shipping Weight (lbs.)	0.03
Shipping Weight (kg)	0.01
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.