


This site uses cookies. By continuing to browse the site you are agreeing to our use of cookies.
[FIND OUT MORE HERE](#)

SEMICONDUCTOR

eMMC

KLM8G1GEUF-B04P



- Overview
- Specifications
- Related resources
- Related insights

Definitive performance for mobile storage

With superior power efficiency and noticeably fast speed, Samsung's eMMC is the definitive choice for flash storage to develop slim mobile design.

Specifications

Version	eMMC 5.1	Density	8 GB
Voltage	1.8 / 3.3 V	Interface	HS400
Package Size	11.5 x 13 x 0.8 mm	Temp.	-40 ~ 85 °C
Product Status	Mass Production		

SEE ALL

Related resources



Samsung Memory Solutions for Automotive



Samsung eMMC

Related insights



Samsung's UFS 3.1: Flash Storage for the 5G Future

Samsung's UFS 3.1 will enable the smartphones of tomorrow to reach new levels of speed, and help pave the way for a new era of exciting mobile experiences.

[LEARN MORE](#)



Samsung Begins Mass Production of the Fastest Storage for Flagship Smartphones

Samsung's new UFS 3.1 breaks the 1GB/s performance threshold in smartphone storage.

[LEARN MORE](#)



Will there be

As Samsung works to vehicles is looking ir

[LEARN MORE](#)

All product specifications reflect internal test results and are subject to variations by user's system configuration. All product images shown are for illustration purposes only and may not be an exact representation of the product. Samsung reserves the right to change product images and specifications at any time without notice.

Newsroom

[Product finder](#)

[Technical resources](#)

[TCO calculator](#)

[About us](#)

PRODUCTS

[DRAM](#)

[SSD](#)

[eSTORAGE](#)

[MCP](#)

[PROCESSOR](#)

[IMAGE SENSOR](#)

[SECURITY SOLUTIONS](#)

[DISPLAY IC](#)

[POWER IC](#)

SOLUTIONS

[APPLICATIONS](#)

[TOPICS](#)

[TECHNOLOGY](#)

Other Sites

[中文\(简体\)](#)

[B2B Workplace](#)

[Memory \(日本語\)](#)

[ISOCELL](#)

[Exynos](#)

[LED](#)

[Display](#)

[Worker Safety](#)

[Samsung Business](#)

Follow us



Copyright © 1995-2020 SAMSUNG All Rights Reserved.

[PRIVACY](#) [LEGAL](#) [SITEMAP](#)

This website is best viewed using Microsoft Internet Explorer 9 or higher, and/or latest version of Google Chrome and Mozilla Firefox browsers.