


[Products](#)[Industries](#)[Resources](#)[About TE](#)[My Account](#)[Innovation](#)[Support Center](#)

[Home](#) > [Products](#) > [Relays](#) > [Product Feature Selector](#) > Product Details

B07D992BB2-0117 Product Details

[Share](#)[Print](#)[Email](#)

 **Active**

Military/Aerospace High Performance Relays

B07D992BB2-0117 = M5757/23-007

B07D992BB2-0117 (1617005-5)

TE Internal Number: 1617005-5

Product Highlights [View All](#)

- 07 Full Size Relay Series
- Input Voltage = 12 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact - Rated Current = 10 A
- Non Polarized, Monostable Coil - Magnetic System

[Pricing & Availability](#)[Request Sample](#)[Add to My Part List](#)[Buy Product through Distributor](#)[Feedback](#)[Documents](#)[Features](#)[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

MOSFET Driver Without

Mechanical Attachment

Mounting Options Chassis Mount

Electrical Characteristics

Input Voltage (VDC) 12

Contact - Rated Current (A) 10

Coil Suppression Diode Without

Coil Polarity Protection Diode Without

Coil - Resistance (Ω) 75

Coil Power Measurement Milliwatts

Coil - Rated Power, DC (mW) 1920

Actuating System DC

Shock 100G's, 6ms

Vibration 20G's, 10 to 2000Hz

Termination Features

Termination Type Solder Hook Terminal

Body Features

Enclosure Type Hermetically Sealed

Configuration Features

Contact - Arrangement 2 Form C, DPDT, 2 C/O

Coil - Magnetic System Non Polarized, Monostable

Transistor Driver Without

Industry Standards

Government/Industry Qualification Yes

Government/Industry Part Number M5757/23-007

RoHS/ELV Compliance Not ELV/RoHS compliant

Lead Free Solder Processes Not suitable for lead free processing

Approved Standards M5757 Qualified

Conditions for Usage

Temperature Range (°C) -65 - +125

Other

Series 07 Full Size Relay

Brand CII

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

