

## Test plugs - MPS-MT/ 4MM - 3048577

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Test plugs, with solder connection up to 1 mm<sup>2</sup> conductor cross section, color: silver

### Your advantages

- ✓ The test plug makes contact in all test sockets with a 4 mm diameter
- ✓ Two-piece test plug for individual plug color combinations

**RoHS**

### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 1 pc  |
| Minimum order quantity               | 10 pc   |
| GTIN                                 | <br>4 046356 072779 |
| GTIN                                 | 4046356072779   |
| Weight per Piece (excluding packing) | 1.000 g   |
| Custom tariff number                 | 85366990  |
| Country of origin                    | Germany   |

### Technical data

#### Dimensions

|                      |                                  |
|----------------------|----------------------------------|
| Length               | 26 mm                            |
| Length contact range | 8.4 mm                           |
| Pin diameter         | 4.4 mm                           |
| Note on dimensions   | Length without insulating sleeve |

#### General

|       |        |
|-------|--------|
| Color | silver |
|-------|--------|

# Test plugs - MPS-MT/ 4MM - 3048577

## Technical data

|                       |                   |
|-----------------------|-------------------|
| Nominal voltage $U_N$ | 60 V DC (30 V AC) |
| Nominal current $I_N$ | 16 A              |

## Environmental Product Compliance

|            |   |
|------------|---|
| REACH SVHC | Lead 7439-92-1  |
| China RoHS | Environmentally Friendly Use Period = 50 years  |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27440313 |
| eCl@ss 11.0   | 27440313 |
| eCl@ss 4.0    | 27141100 |
| eCl@ss 4.1    | 27141100 |
| eCl@ss 5.0    | 27141100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27141100 |
| eCl@ss 7.0    | 27440313 |
| eCl@ss 9.0    | 27440313 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000899 |
| ETIM 3.0 | EC000899 |
| ETIM 4.0 | EC002255 |
| ETIM 6.0 | EC002255 |
| ETIM 7.0 | EC002255 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211812 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121411 |
| UNSPSC 12.01  | 39121411 |
| UNSPSC 13.2   | 39121410 |
| UNSPSC 18.0   | 39121410 |
| UNSPSC 19.0   | 39121410 |
| UNSPSC 20.0   | 39121410 |
| UNSPSC 21.0   | 39121410 |

# Test plugs - MPS-MT/ 4MM - 3048577

## Approvals

Approvals

Approvals

EAC

Ex Approvals

## Approval details

|     |   |                          |
|-----|---|--------------------------|
| EAC |  | RU C-<br>DE.BL08.B.00511 |
|-----|---|--------------------------|

## Accessories

### Accessories

#### Insulating sleeve

Insulating sleeve - MPS-IH BK - 0201731

Insulating sleeve, color: black



Insulating sleeve - MPS-IH RD - 0201676

Insulating sleeve, color: red



## Test plugs - MPS-MT/ 4MM - 3048577

### Accessories

Insulating sleeve - MPS-IH GN - 0201702

Insulating sleeve, color: green



---

Insulating sleeve - MPS-IH GY - 0201728

Insulating sleeve, color: gray



---

Insulating sleeve - MPS-IH BU - 0201689

Insulating sleeve, color: blue



---

Insulating sleeve - MPS-IH YE - 0201692

Insulating sleeve, color: yellow



---

Insulating sleeve - MPS-IH WH - 0201663

Insulating sleeve, color: white



