

Connectors > Rectangular Connectors > Rectangular Contact Inserts

697119-000 ACTIVE

Rectangular Contact Inserts, Contact Insert, Socket, Wire-to-Wire, 10 Position, Sealable, 20 – 26 AWG Wire Size, RAYCHEM MTC100



RAYCHEM | RAYCHEM MTC100

TE Internal #: 697119-000  
 TE Internal Description: MTC100-JB1-S14  
 Alias #: 7-1195471-0

Rectangular Connector Insert Type : **Contact Insert**  
 Contact Type : **Socket**  
 Connector System : **Wire-to-Wire**  
 Number of Positions : **10**  
 Centerline (Pitch) : **1.27 mm [.05 in]**


[Add to List](#) | [Similar Products](#) | [Digital Datasheet](#)

[Compatible Parts & Tooling](#)

Documents	Features	Product Compliance
Please review product documents or <a href="#">contact us</a> for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.		
Product Type Features	Rectangular Connector Insert Type : <b>Contact Insert</b> Connector System : <b>Wire-to-Wire</b> Sealable : <b>Yes</b> Connector & Contact Terminates To : <b>Wire &amp; Cable</b>	
Configuration Features	Number of Positions : <b>10</b>	
Body Features	Primary Product Color : <b>Black</b> Primary Product Material : <b>High Grade Polyarylene Thermoplastic</b>	
Contact Features	Contact Type : <b>Socket</b> Contact Current Rating (Max) (A): <b>1.5</b>	
Mechanical Attachment	Polarization Code : <b>B</b> Connector Mounting Type : <b>Panel Mount</b>	
Housing Features	Centerline (Pitch) : <b>1.27 mm [.05 in]</b>	
Dimensions	Wire Size (AWG): <b>20 – 26</b> Wire Size (mm <sup>2</sup> ): <b>.5 – .14</b>	
Usage Conditions	Operating Temperature Range : <b>-65 – 125 °C [-85 – 257 °F]</b>	
Operation/Application	Compatible With Connector Shell Size : <b>25.4 [1.0]</b>	
Packaging Features	Packaging Quantity : <b>1</b>	

**THIS PART IS OUT OF STOCK**


**Similar Parts In Stock**



Rectangular Contact Inserts, Contact Insert, Pin, Wire-to-Wire, 10 Position...

TE Part #: 697118-000

[View Product](#)




Rectangular Contact Inserts, Contact Insert, Socket, Wire-to-Wire, 10...


TE Part #: 699232-000


[View Product](#)

[View All Similar Parts](#)

**We are here to help!**  
Get in touch with our product experts.

 [CHAT WITH US](#)

 [EMAIL US](#)

 [CALL US](#)

[REPORT PRODUCT DATA ERROR](#)





### Compatible Parts

There are no compatible parts for this product. Please reach out to Product Support to help with your request.






[Contact Product Support](#)

### Products with Similar Specs





[View All Similar Products](#)

THIS PRODUCT	TOP RESULTS		
<p>RECTANGULAR CONTACT INSERTS <b>697119-000</b></p> <p>Rectangular Contact Inserts, Contact Insert, Socket, Wire-to-Wire, 10...</p>  <p style="text-align: center;">Non-Stocked</p> <p>Rectangular Connector Insert Type : <b>Contact Insert</b>                      Contact Type : <b>Socket</b>                      Connector System : <b>Wire-to-Wire</b>                      Number of Positions : <b>10</b>                      Centerline (Pitch) : <b>1.27 mm</b></p>	<p>RECTANGULAR CONTACT INSERTS <b>MTC100-JB1-S11</b></p> <p>Rectangular Contact Inserts, Contact Insert, Socket, Wire-to-Wire, 10...</p>  <p style="text-align: center;">Non-Stocked</p> <p>Rectangular Connector Insert Type : <b>Contact Insert</b>                      Contact Type : <b>Socket</b>                      Connector System : <b>Wire-to-Wire</b>                      Number of Positions : <b>10</b>                      Centerline (Pitch) : <b>1.27 mm</b></p>	<p>RECTANGULAR CONTACT INSERTS <b>697118-000</b></p> <p>Rectangular Contact Inserts, Contact Insert, Pin, Wire-to-Wire, 10 Position...</p>  <p style="text-align: center;">In-Stock</p> <p>Rectangular Connector Insert Type : <b>Contact Insert</b>                      Contact Type : <b>Pin</b>                      Connector System : <b>Wire-to-Wire</b>                      Number of Positions : <b>10</b>                      Centerline (Pitch) : <b>1.27 mm</b></p>	<p>RECTANGULAR CONTACT INSERTS <b>MTC100-JB1-P11</b></p> <p>Rectangular Contact Inserts, Contact Insert, Pin, Wire-to-Wire, 10 Position...</p>  <p style="text-align: center;">Non-Stocked</p> <p>Rectangular Connector Insert Type : <b>Contact Insert</b>                      Contact Type : <b>Pin</b>                      Connector System : <b>Wire-to-Wire</b>                      Number of Positions : <b>10</b>                      Centerline (Pitch) : <b>1.27 mm</b></p>

### Customers Also Bought

 <p>TE Part #: <b>202K132-100-0</b></p> <p>Heat Shrink Boots, Straight, Size 202, Lipped, 100, 100...</p> <p>\$21,290 per unit Inventory: In-Stock</p> <p><a href="#">Add To Cart</a></p>	 <p>TE Part #: <b>HT-SCE-1/8-2.0-9</b></p> <p>Printable Tubing, Ladder, High Temperature, 2:1...</p> <p>\$8,142 per unit Inventory: In-Stock</p> <p><a href="#">Add To Cart</a></p>	 <p>TE Part #: <b>697117-000</b></p> <p>Rectangular Contact Inserts, Contact Insert, Socket...</p> <p><a href="#">View Product</a></p>	 <p>TE Part #: <b>047-0893-20</b></p> <p>Socket Contact, Gold, 115 VAC, 115 VDC, Spring...</p> <p><a href="#">View Product</a></p>	 <p>TE Part #: <b>047-1024-20</b></p> <p>Pin Contact, Gold, 115 VAC, 115 VDC, Spring Contact...</p> <p><a href="#">View Product</a></p>
----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

### Also in the Series | RAYCHEM MTC100

 <p>Heat Shrink Tubing (11)</p>	 <p>Rectangular Connector Housings (8)</p>	 <p>Rectangular Contact Inserts (32)</p>	 <p>Standard Rectangular Connectors (28)</p>
--------------------------------------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------	-----------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------

**Contact Our Team – 24/7 Support**  
 +1 800 522 6752  
 [Live Chat](#)  
[See Support Details](#)

**Connect With Us**  
    

**Access Partner Information**  
[Distributors](#)  
[Suppliers](#)  
[Supplier Diversity](#)

**Get Answers Now**  
[Authorized Distributors & Resellers](#)  
[Product FAQs](#)  
[Samples FAQs](#)  
[TE Store FAQs](#)  
[Terms and Conditions of Sale](#)  
[Samples Terms and Conditions](#)

**Select Your Preferences**  
 **Language**  
[English \(EN\)](#)  
**Ship to**  
 [United States \(\\$USD\)](#)