

Part Number : [02066103](#)

Product Description : 1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Gold (Au) Plated Brass Contact, 24-18 AWG, Bag

Series Number : 1560

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 1560-(550)L

Packaging Alternative : [02066100](#) (Reel)



Documents and Resources


Drawings

[002066103 sd.pdf](#)

[PK-1190-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	1560
Description	1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Gold (Au) Plated Brass Contact, 24-18 AWG, Bag
Application	Power, Wire-to-Wire
Product Name	Standard .062"
UPC	800753615823

Physical

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.127/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.254µm
Wire Insulation Diameter	1.52-3.05mm
Wire Size (AWG)	18, 20, 22, 24
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Insertion Tool for Standard .062" Diameter Male and Female Terminals	<u>11020001</u>
Extraction Tool for Standard .062" and Standard .062"+ Pin and Socket Terminals	<u>11030002</u>
ServiceGrade Hand Crimp Tool for Field Repair Only, 24-14 AWG	<u>638111000</u>
Hand Crimp Tool for Standard 1.57mm Pin and Socket Crimp Terminals, 24-18 AWG	<u>638191300</u>

This document was generated on May 09, 2026