

**SCHROFF**

Project - 0 item(s)

MY PROJECT LIST

PRODUCTS

APPLICATIONS

INDUSTRIES

NEW PRODUCTS

CONFIGURATORS

Products ▾

Search



Home > Plug in unit kit, front anodized and rear conductive, shielded (textile), front assembly, with IEL handle

**SCHROFF**

Plug in unit kit, front anodized and rear conductive, shielded (textile), front assembly, with IEL handle

Catalog Number: 20848-592[Back To Product](#)

- Front panel, shielded
- Designed for fitting of microswitches
- Suitable for insertion and extraction forces up to 700 N (per pair)
- To IEEE 1101.10 and IEC 60297-3-102
- Codable to IEC 60297-3-103/ IEEE 1101.10

Plug in unit, 6 U, front anodized, rear etched, shielded (textile), front or rear IO assembly, IEL handle

Specification:

- IEC 60297-3-103
- IEC 60297-3-102
- IEEE 1101.10
- IEEE 1101.1/11

Material and Surface Finish:

Al, Front Anodized, Rear Etched

Product family:

Plug-in units

Handle:

IEL

Assembly:


- Screw on - Front Side
- Screw on - Rear IO

EMC Shielding:


Shielded (Textile Gasket)

Standard:

CompactPCI, CompactPCI Serial, VME64x, VXS, VPX



Other Views



Select product specifications before modifying or adding to project list or requesting a quote.

Height-U-defining

6 ▾

Width-HP-defining

4 ▾

[Clear Selection](#)Quantity

Modify Product ►

Add Item to Project List +

Documents

User manual, coding IEEE



User manual, plug-in unit IEEE



User Manual



Dimension, Front panel 3 / 6 U



Main Catalog - Plug-in units



Links

Native CAD files

Technical Data**For case height [U]** 261.8**Thickness mm** 2.5**Height U** 6**Width HP** 4**Delivery Comprises:**

Item	Quantity	Description
1	1	Front panel (U profile), Al, front anodized, rear conductive
2	1	EMC sealing (textile), core: foam, sleeve: textile cladding, CuNi coated

Item	Quantity	Description
3	1	Handle with integrated alignment pin for perforated strips and guide rails, lever: plastic, PC, black, RAL 9005 Key: Plastic, PC, light gray, RAL 7035
4	2	Pozidrive collar screw, M2.5 × 12.3, St, nickel-plated
5	2	Panhead screw with Torx/slot, M2.5 × 6, St, zinc-plated, selflocking
6	2	Washer A2.7, DIN 125, St, nickel-plated
7	2	Panhead screw with Torx, M2.5 × 7, St, nickel-plated

Accessories			
	Microswitch for IEL/IET handle, PU 10 pcs	20817-606	Add Item to Project List +
	Label strips for IEL/IET handle, white, sheet with 210pcs (19x9,5), PU 1 pcs	60817-340	Add Item to Project List +
	Label strips for IEL handle, white, sheet with 320pcs (19x4,8), PU 1 pcs	60817-341	Add Item to Project List +
	VME-based systems (VXS, VPX)	20836-820	Add Item to Project List +
	VME-based systems (VXS, VPX)	20836-220	Add Item to Project List +

EXPLORE	CONTACT	DOWNLOAD
About Us	Customer Service	Download Center
Services & Capabilities	Find a Sales Office or Distributor	Reference Projects
News & Events	Global Locations	Videos
Newsletter Subscriptions	Product Compliance & Certifications	Product Configurators
Strategic Partnerships	Partner Login	Warranties and Terms of Sale & Procurement
Investor Relations		

Connect With Us

