

Part Number : [08500133](#)

Product Description : KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 2.540µm Tin (Sn)

Series Number : 2578

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 2578-B-P909

Packaging Alternative : [08500134](#) (Bag)



Documents and Resources

Drawings

[008500133_sd.pdf](#)

[PK-2759-002-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-08-50-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	2578
Description	KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 2.540µm Tin (Sn)
Application	Power, Wire-to-Board
Product Name	KK 396, KK 508
UPC	800754224666

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.150/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.65mm max.
Wire Size (AWG)	22, 24, 26
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
KK 3.96mm Single Row Crimp Housings	<u>2139</u>
KK 3.96mm Single Row Crimp Housings	<u>3069</u>
KK 3.96mm Crimp Housings	<u>41695</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals	<u>11030016</u>
PremiumGrade Hand Crimp Tool for KK 3.96mm Terminals, 26-22 AWG	<u>638117400</u>
Mini-Mac Applicator	<u>638881000</u>

This document was generated on Apr 11, 2026