


[About ASSMANN](#)
[Career](#)
[Our Brands](#)
[Portfolio](#)
[Products](#)
[Press](#)
[Services](#)
[Contact](#)
[Business Shop](#)



PRODUCTS

[Network and Server Cabinet Systems](#)
[Network Infrastructure](#)
[Fiber Optic Solutions](#)
[Network / KVM / Video solutions](#)
[Security solutions](#)
[Presentation solutions](#)
[Smart Home solutions](#)

Cables

[Blister Assortment](#)
[Network Cables](#)
[Fiber Optic Cables](#)
[DisplayPort](#)
[HDMI](#)
[DVI](#)
[VGA](#)

USB

[USB 2.0 Cables USB A Plug to USB A Plug](#)
[USB 2.0 Cables USB A Plug to USB B Plug](#)
[USB 2.0 Cables USB A Plug to USB mini 4-Pin](#)
[USB 2.0 Cables USB A Plug to USB mini 5-Pin](#)
[USB 2.0 Cables USB A Plug to micro USB Type B](#)
[USB 2.0 Cables USB A Plug to USB A Jack](#)
[USB 2.0 and USB 3.0 Adapters / Slot-Brackets](#)
[USB 3.0 Cables USB A Plug to USB B Plug](#)
[USB 3.0 Cables USB A Plug to micro USB Type B](#)
[USB 3.0 Cables USB A Plug to USB A Jack](#)
[USB Type-C Cables](#)
[Serial / Parallel / Printer](#)
[Internal PC Cables / SATA](#)
[Firewire / Thunderbolt / MHL](#)
[Device Connection Cables](#)
[Audio- / Video Cables](#)
[Telecommunications Cables](#)
[TV/SAT Cables](#)
[Apple](#)
[MHL](#)
[Tablet and Smartphone Cables](#)
[Accessories](#)
[USB Type-C™](#)
[Computer Accessories and Components](#)
[Power Supplies and Charging](#)
[Mobility](#)

Small Office Home Office
Downloaded from [Arrow.com](#)

Products

ASSMANN Micro USB 2.0 connection cable

AK-300127-010-S

EAN 4016032314639

[Print version](#)

USB 2.0


Description

USB connection cable, type A - micro B M/M, 1.0m, USB 2.0 compatible, bl

Allows a reliable and fast connection of external USB devices with the PC, also about longer distances.

For connection of external USB devices (with USB micro B socket, e.g. MP3 -player, smart phone or external HDD enclosure) to the USB host (e. g. PC, notebook or USB hub). Data transfer rate up to 480 Mbps (High-Speed).

Technical Details

- Connector 1: USB A, plug
- Connector 2: Micro USB B, plug
- Hoods: molded
- Connector surface: nickel-plated
- Color cable: black
- Color connector: black
- Length: 1 m
- Assortment: USB Cables
- USB compliance: USB 2.0

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	300	12,00	45,00	32,00	25,00	36000,00
Packaging Unit Inside	10	0,40	24,00	21,00	3,00	1512,00
Packaging Unit Single	1	0,04	19,00	16,00	1,00	304,00
Net single without Packaging	1	0,04	19,00	16,00	1,00	304,00

ABOUT ASSMANN

- ASSMANN Management
- Awards
- ASSMANN Offer
- ASSMANN Product Management
- Quality Management



SERVICES

- Catalogs
- Subscribe Newsletter
- Software & Firmware
- ABRAM
- Business Shop
- System Warranty

HIGHLIGHTS



➔ ASSMANN
12 Oct.

ednet Slim Line Aluminium Power
Bank

➔ plugilo

SUBSCRIBE
NEWSLETTER

IMPRINT

DISCLAIMER

DATA PROTECTION

SITEMAP

CAREER



Copyright © 2018 ASSMANN