



SCHROFF

Project - 0 item(s)


MY PROJECT LIST

- PRODUCTS
- APPLICATIONS
- INDUSTRIES
- NEW PRODUCTS
- CONFIGURATORS
- Products ▾
- Search
-

Home > EN 60603 (DIN 41612) Connector, Type C

EN 60603 (DIN 41612) Connector, Type C

SCHROFF



Catalog Number: 69001-816

[Back To Product](#)

- Requirement class 2 as per EN 60603 (DIN 41642)

Note:

Requirement class 2 as per EN 60603 (DIN 41642)

Description:

Connector


Product family:

PCB Accessories



View of rear of plug

Other Views



Select product specifications before modifying or adding to project list or requesting a quote.

[Clear Selection](#)

Quantity

Add Item to Project List +


Documents

- Main Catalog - Connectors, busbars
- User Information

Technical Data

Qty	1 piece	Connector pitch [mm]	2.54
Number of contacts	96	Creepage distances contact-contact [mm]	> 1.2
Row assignment	a, b, c	Current load max. at 20 °C [A]	2
Other	Male connector	Test voltage Ueff contact-contact [kV]	1
Connector	Solder pins, length 3 mm, 0.6 mm x 0.6 mm; angled	Test voltage Ueff contact-earth [kV]	1.55
		Contact resistance [mΩ]	≤ 20
		Separate coding	yes
		Contact surface	solidly gold-plated
		Insertion and withdrawal forces [N]	< 90 N
		Air gap contact-contact [mm]	> 1.2

Accessories



Panhead screw, Torx (M2.5x7), steel nickel plated, PU 100 pcs

24560-147

[Add Item to Project List +](#)

EXPLORE

- [About Us](#)
- [Services & Capabilities](#)
- [News & Events](#)
- [Newsletter Subscriptions](#)
- [Strategic Partnerships](#)
- [Investor Relations](#)

CONTACT

- [Customer Service](#)
- [Find a Sales Office or Distributor](#)
- [Global Locations](#)
- [Product Compliance & Certifications](#)
- [Partner Login](#)

DOWNLOAD

- [Download Center](#)
- [Reference Projects](#)
- [Videos](#)
- [Product Configurators](#)
- [Warranties and Terms of Sale & Procurement](#)

© 2018 nVent. All rights reserved | [Privacy Policy](#) | [Terms of Use](#) | [Cookie Policy](#) | [Imprint](#) | [Site Map](#)

Connect With Us

