



REVISIONS			
REV	ECN	DESCRIPTION	DWN CHK DATE
A	-	Initial release.	AMH - 04-01-09
B	-	Updated spec and label	AMH - 10-30-09
C	-	Changed pin out definition	AMH - 11-03-09

FRONT VIEW



NOTES: B

1. Operation Temperature: -20°C ~ +60°C
Storage Temperature: -20°C ~ +70°C
2. Life Time: >5,000,000 times.
3. Linearity: ≤ 1.5%.
4. ITO Film: Anti-glare & Hardening Coating Anti-Newton Ring
Sheet Resistance: 400±100 Ohm/square;
ITO Glass: Sheet Resistance: 400±100 Ohm/square
5. Tail Type: Gold plated FPC
6. All Tolerance Without Marked: ±0.3
7. All Materials and Components must be RoHS compliant
8. No Material is allowed to be larger than the glass size

		CUSTOMER NAME Agilent	UNIT mm [inch]	DAWAR P/N 5059-000	REV C
		CUSTOMER P/N 5059-000	REV C	MANUFACTURING NO. KDT-1555	REV 3
		DESCRIPTION 15.0" 8-Wire Resistive Touch Screen	SHEET 1 OF 1	DRAWN BY Jason Liao	DATE 11-03-09
		CUSTOMER APPROVAL SIGNATURE: DATE:			

THIS DOCUMENT IS THE PROPERTY OF DAWAR TECHNOLOGIES, INC. AND SHALL NOT BE COPIED, REPRODUCED, DISCLOSED, OR USED AS THE BASIS FOR ANY MANUFACTURING OR SALE WITHOUT PERMISSION OF A DULY AUTHORIZED REPRESENTATIVE OF DAWAR TECHNOLOGIES, INC.