





LEOPARD IMAGING INC

Rev. 1.0

Key Features

- USB 3.0 Super Speed support
- RAW data output without compression
- UVC compliance
- USB 2.0 backwards compatible
- Support External Trigger, Software Trigger
- Support either CS or M12 lens
- Provide customization services
- USB +5VDC powered device
- Compact Size: 26mmx26mm
- 2 Boards are stacked
- Part#: **LI-USB30-IMX225C**



RAW data streaming



Camera Tool view mode

LI-USB30-IMX225C

Data Sheet



Default Lens Specification

- Model: M13B0618WR5
- Image format: 1/3"
- Focal length: 6.0 mm
- Aperture, F/#: 1.8
- Built in 650nm IR cut filter
- FOV (D/H/V): 60 °/ 48 °/34.5 °
- Mount: M12 x 0.5 – 6g

Applications

- Machine Vision
- Medical Camera
- Scientific Camera

SDK Supported

- Camera Tool Source Code in C#
- Capture & Display
- OpenCV supported through Emgu
- RAW to RGB Conversion
- Save file as BMP & RAW format



Leopard Imaging Inc.

1130 Cadillac Ct., Milpitas, CA 95035, USA

Phone: +1-408-263-0988

Fax: +1-408-217-1960

Email: sales@leopardimaging.com

Website: www.leopardimaging.com

www.leopard-security.com

Specification

General Behavior	
Video Resolution @ Frame rate	1312 x 992 @ 30 fps
Sensitivity	TBD
Dynamic range	12 bit
Trigger mode	External Trigger, Software Trigger
Interface (Optical)	
IR cut filter	Yes
Sensor specification	Sony Diagonal 6.09 mm (Type 1/3) CMOS Solid-state Image Sensor IMX225
Shutter	Rolling
Format	1/3"
Total number of pixels	H:1312, V:993
Pixel size	H:3.75 um, V: 3.75 um
Lens mount	CS / M12 lens mount support (Default: M12 lens)
M12 Lens	6.0 mm (default), 4.2 mm, 2.6 mm Focal Length
Interface (Electrical)	
Interface	USB 3.0
Supply voltage	USB 3.0 +5 VDC power source
Current consumption	Approx. 175 mA at 5 VDC
Interface (Mechanical)	
Dimensions	L: 26 mm, W: 26 mm, H: 38 mm
Mass	22 g
Adjustment (Manual)	
Shutter	TBD
Gain	TBD
Adjustment (Auto)	
Shutter	TBD
Gain	TBD
Environmental	
Max. temperature (operation)	0 °C ~ 50 °C (32 °F~ 122 °F)
Max. temperature (storage)	-20 °C ~ 80 °C (-4 °F~176 °F)
Max. humidity (operation)	20 % ~ 80 %, relative, non-condensing
Max. humidity (storage)	20 % ~ 80 %, relative, non-condensing



Leopard Imaging Inc.

1130 Cadillac Ct., Milpitas, CA 95035, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com
www.leopard-security.com