

Technical specification :

Rated voltage: IEC 61076-2-104	30 V
Current rating: IEC 61076-2-104	3 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Coupling screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:



Recommended torque:	0,4 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 9: 36-000210

Contact assignment:

1	■	brown
2	■	white
3	■	blue
4	■	black

Part no:	Description:	Length L:	Cable:
42-10060	SAL - 8 - RSW4 - 2 / K1	2m	TPU, UL 20549, black, 4x0,25mm ² Cable: 781-K12400
42-10061	SAL - 8 - RSW4 - 3 / K1	3m	
42-10062	SAL - 8 - RSW4 - 5 / K1	5m	
42-10063	SAL - 8 - RSW4 - 10 / K1	10m	
42-xxxxx	SAL - 8 - RSW4 - ... / K1	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: b 16.03.11 VF Ä3945 Coupling screw modified, spanner flats added, data sheet modified		 dim. in mm		title: Male connector M8x1 angled	
				date		
	tolerance of cable:	L <= 4m: L + 40mm L > 4m: L + 1%	drawn	04.10.07	Franz	dwg no: 42K1A016
			appd.	04.10.07	Mankopf	
	general tolerance:	0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm				part no: see table

CONEC®