

MICRO SWITCHFREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929**SWITCH - BASIC**

CATALOG LISTING

BZ-RW847225-A2

ANN0210

BZ-RW847225-A2**M**DRAWING
NUMBER

4

ISSUE

REVISIONS

A	CO-73287-J	22 NOV 93
B	CO93346	25 NOV 05
C	0015929	25 NOV 05

REPLACES X65673-BZ

PAGE 1 OF 1

CHECK

25 NOV 05

RJ

CHECK

23 SEPT 76

CHECK

CEB

CHECK


23 SEPT 76

GLH

RASTER

FO-52648-A


DRAWN

**NOTES**

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX. DIA. ON 1.000 ± .002 CENTERS
- 2 FORCES MEASURED WITH LEVER IN VERTICAL POSITION AT POINT "A" WITH CONTACT END OF SWITCH DOWN
- 3- CONTACT MATERIAL - GOLD ALLOY

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS AT POINT "A"**

OPERATING FORCE --- 10 GRAM MAX



DIFFERENTIAL TRAVEL --- .002-.009

OVERTRAVEL --- .125 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D T

CODE L22 1A-125 VAC

L288
L315
L307

1A 250V ~ T85 25E3

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 2

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/64	
ONE PLACE	X,X	0.4/0.16	X X
TWO PLACES	X,XX	0.15/0.06	X X X
THREE PLACES	X,XXX	0.38/0.15	X X X X
ANGLES		0.13/0.05	

DESIGN UNITS

SI METRIC

US CUSTOMARY

WEIGHT .073 LB.