



ML23HSAL4500-E

Stepper motor,Double shaft, High torque, Low inertia, Fast raising speed, 2 phase, 1.8°, NEMA23

- Low Inertia, Quick Response
- High Torque, High Efficiency
- Low Vibration, Low Noise
- Available options for Drives, Flexible Coupling, Damper

Learn More About NEMA 23 Standard Hybrid Stepper Motors



Specification Torque Speed Curves Mechanical Size Downloads Recommended Options Delivery & Packaging

Parameter	Unit	Value
Phase		2
Step Angle		1.8°
Shaft		Double
Frame Size		NEMA23(56.4mm)
Length	m m	77
Rated Current	A	5
Holding Torque	Nm	2.3
Holding Torque	oz-in	325.73
Resistance	Ohms ±10%@20°C	0.39
Inductance	mH Typ.	1.53
Coil Type		Bi-Polar
Detent Torque	mNm	75
Rotor Inertia	gcm²	391
Front Shaft Length	m m	20.6
Front Shaft Diameter	m m	6.35
Rear Shaft Length	m m	13
Rear Shaft Diameter	m m	6.35
Terminal Number		4
Connect		Leads
Insulation Class		B(130°C)
Approvals		UL,RoHS
IP Rating		IP40
Weight	kg	1



SR8-Plus

Supply Voltage:24VDC-75VDC, Output Current(peak):2.4Amps-7.8Amps, Step Resolutions(1.8°Stepper): Full Step, 2x, 4x, 5x, 8x, 10x, 16x, 20x, 25x, 32x, 40x, 50x, 64x, 100x, 125x, 128x Microstepping, Step Pulse Frequency:2MHz Max, Selectable Damping Modes For Smooth Motion



Damper00014

Shock Absorber, Vibration Damper for Stepper Motor



AMT102-C1

Modular Incremental Encoder

Filter By Product Type

- ☒ All Products
- ☐ Drives
- ☐ Encoder
- ☐ Damper



MOONS'

moving in better ways

As one of the largest integrated manufacturers of motion control and intelligent lighting products within China, MOONS' has professional teams of research and development, manufacturing, sales and technical support all over the world. Our website (www.moonsindustries.com) is the first professional E-business platform in this industry, on which an extremely wide range of high performance motion control and intelligent lighting products are supplied to customers around the

ALL OF US

Products

Applications

Blog & Videos

Products Launch

About Us

Careers

WorldWide

Custom Designs

Contact Us

NEWSLETTER SIGN UP

SUBSCRIBE



We use cookies on this website to enhance your user experience.

And we have updated our Privacy Policy. Please read our privacy policy to give your consent to it. Thanks. [Learn more](#)

Got it