

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0875681493**
Status: **Active**
Overview: Milli-Grid Connector System
Description: Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 14 Circuits, 0.38µm Gold (Au) Selective Plating, with Center Polarization Key and Locking Friction Ramp

Documents:

[3D Model](#) [Packaging Specification PK-87568-0001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-87568-004-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family IDT and Solder Connectors
 Series 87568
 Crimp Quality Equipment Yes
 Overview Milli-Grid Connector System
 Product Name Milli-Grid
 UPC 822348457595
 Use With 87569-1014 Strain Relief (Optional)

Physical

Circuits (Loaded) 14
 Circuits (maximum) 14
 Color - Resin Black
 Durability (mating cycles max) 100
 Flammability 94V-0
 Gender Female
 Glow-Wire Capable No
 Lock to Mating Part Yes
 Material - Metal Copper Alloy
 Material - Plating Mating Gold
 Material - Resin Polyester
 Net Weight 939.720/mg
 Number of Rows 2
 Packaging Type Tray
 Panel Mount No
 Pitch - Mating Interface 2.00mm
 Polarized to Mating Part Yes
 Stackable No
 Temperature Range - Operating -20° to +85°C
 Termination Interface: Style IDT or Pierce
 Wire Size AWG 28

Electrical

Current - Maximum per Contact 1.0A
 Voltage - Maximum 125V


Solder Process Data

Lead-free Process Capability N/A

Material Info

Reference - Drawing Numbers

Packaging Specification PK-87568-0001-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

87568 Series

Mates With

87831 Vertical PCB Header, 87832 Surface Mount PCB Header, 87833 Right Angle PCB Header

This document was generated on 10/09/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION