

# Metal thin film chip resistors (precision)

## ■ RR series

### Features

- Excellent characteristics in resistance tolerance, temperature coefficient of resistance, current noise, and linearity

### Applications


- Any electronics applications that require accuracy and reliability such as automotive electronics, industrial test and measurement, consumer electronics and many others.

### Specifications

\* Stocked items: E-24 series (TCR P and Q, resistance tolerance D), other E-24 and E-96 series are made to order.

#### ▣ Dimensions

unit : mm



Dimension (inch)	RR0306 (0201)	RR0510 (0402)	RR0816 (0603)	RR1220 (0805)	RR1632 (1206)	RR2632 (1210)
L	0.60±0.05	1.00±0.05	1.60±0.20	2.00±0.20	3.20±0.20	3.20±0.20
W	0.30±0.05	0.50±0.05	0.80±0.20	1.25±0.20	1.60±0.20	2.60±0.20
A	0.12±0.05	0.20±0.10	0.30±0.20	0.40±0.20	0.50±0.20	0.50±0.20
B	0.12±0.05	0.25±0.05	0.30±0.20	0.40±0.20	0.45±0.20	0.45±0.20
T	0.23±0.03	0.35±0.05	0.40±0.10	0.40±0.10	0.40±0.10	0.40±0.10

#### ▣ Electrical characteristics

Series name		RR0306		RR0510		RR0816		RR1220		RR1632			RR2632		
power		1/20W		1/16W		1/16W		1/10W		1/8W			1/4W		
E series offered		E-24		E-24, E-96											
Resistance range (Ω)		10 ~ 30	33 ~ 22k	10 ~ 91	100 ~ 100k	10 ~ 91	100 ~ 360k	10 ~ 91	100 ~ 1M	10 ~ 47	51 ~ 1M	100 ~ 200k	10 ~ 47	51 ~ 1M	100 ~ 200k
Resistance tolerance (%)	±0.1% (B)	—	—	—	—	—	—	—	—	—	—	—	—	—	—
	±0.5% (D)	—	○	○	○	○	○	○	○	○	○	—	○	○	○
	±1.0% (F)	○	—	—	—	—	—	—	—	—	—	—	—	—	—
Temperature coefficient of resistance (ppm/°C)	±5 (V)	—	—	—	—	—	—	—	—	—	—	○	—	—	○
	±10 (N)	—	—	—	—	—	—	—	—	—	—	○	—	—	○
	±25 (P)	—	○	—	○	—	○	—	○	—	○	○	—	○	○
	±50 (Q)	—	—	—	—	○	—	○	—	○	—	—	○	—	—
	±100 (R)	○	—	○	—	—	—	—	—	—	—	—	—	—	—
Maximum voltage		15V		25V		75V		100V		150V			200V		
Operating temperature		-55°C~125°C													
Packaging	5,000pcs	○		—		○		○		○		○		○	
	10,000pcs	—		○		—		—		—		—		—	

Contact us for the jumper resistor in RR0816 size (part number: RL0816-JMP)

### Part numbering system

**RR 0816 P - 102 - D - (M) - (T5) - (\*\*\*)** — Only given to 3 digit codes for RR0816 E-96 series

