

SuperServer 5028R-WR

Products ▶ Systems ▶ 2U ▶ [5028R-WR]



Integrated Board



Super X10SRW-F

Key Features

- 5x PCI-E x8, 8x 3.5" Drives
- Cost-effective, Single Socket

1. Single socket R3 (LGA 2011) supports Intel® Xeon® processor E5-2600 v4[†]/ v3 family; QPI up to 9.6GT/s
2. Intel® C612 chipset
3. 8x 3.5" Hot-swap SATA3 drive bays; optional fixed drive bays
4. Up to 1TB[†] ECC 3DS LRDIMM , up to DDR4- 2400[†]MHz ; 8x DIMM slots
5. 5x PCI-E 3.0 x8 slots via riser card
6. Intel® i350-AM2 Dual port GbE LAN
7. 1x Slim DVD ROM drive bay (option)
8. 2x USB 2.0 ports, 2x USB 3.0 ports
9. 500W Redundant Power Supplies **Platinum Level (94%+)**
10. 3x middle cooling fans

Available Colors:

Black



▶ [Drivers & Utilities](#) ▶ [BIOS](#) ▶ [IPMI](#) ▶ [Tested Memory](#) ▶ [Manuals](#) ▶ [OS Certification Matrix](#) ▶ [Quick-References Guide](#) ▶ [Drive Options](#)

Note: Image above may show a varied configuration or optional parts. Please refer to parts list for standard parts included.

Specifications

Product SKUs

SYS-5028R-WR ■ SuperServer 5028R-WR (Black)

Motherboard

Super X10SRW-F

Processor

CPU ■ Intel® Xeon® processor E5-2600 v4[†]/ v3, E5-1600 v4[†]/ v3 family (up to 145W TDP **)
■ Single Socket R3 (LGA 2011)

Core / Cache ■ Up to 22 Cores[†] / Up to 55MB[†] Cache

Note [†] BIOS version 2.0 or above is required

Note ** Motherboard supports this maximum TDP. Please verify your system can thermally support

System Memory

Memory Capacity ■ 8x 288-pin DDR4 DIMM slots
■ Up to 1TB ECC 3DS LRDIMM
■ Up to 512GB ECC LRDIMM
■ Up to 256GB ECC RDIMM

Memory Type ■ 2400[†]/ 2133/1866/1600MHz ECC DDR4 SDRAM 72-bit, 288-pin (RDIMM / LRDIMM) / 284-pin gold-plated DIMMs

DIMM Sizes ■ 3DS LRDIMM: 128GB
■ LRDIMM: 64GB, 32GB
■ RDIMM: 32GB, 16GB, 8GB, 4GB

Memory Voltage ■ 1.2 V

Error Detection ■ Corrects single-bit errors
■ Detects double-bit errors (using ECC memory)

On-Board Devices

Chipset ■ Intel® C612 chipset

SATA ■ SATA3 (6Gbps) via C612 controller
■ RAID 0, 1, 10 support

IPMI ■ Support for Intelligent Platform Management Interface v.2.0
■ IPMI 2.0 with virtual media over LAN and KVM-over-LAN support
■ ASPEED AST2400 BMC

Network Controllers ■ Intel® i350-AM2 Dual Port Gigabit Ethernet
■ Virtual Machine Device Queues reduce I/O overhead
■ Supports 10BASE-T, 100BASE-TX, and

Chassis

Form Factor ■ 2U Rackmount

Model ■ [CSE-825TQ-R500WB](#)

Dimensions

Height ■ 3.5" (88.9mm)

Width ■ 17.2" (437mm)

Depth ■ 25.5" (648mm)

Package ■ 11" (H) x 26.5" (W) x 34.5" (D)

Weight ■ Gross Weight: 59 lbs (26.7 kg)
■ Net Weight: 34 lbs (15.4 kg)

Available Colors ■ Black

Front Panel

Buttons ■ Power On/Off button
■ System Reset button

LEDs ■ Power LED
■ Hard drive activity LED
■ 2x Network activity LEDs
■ System Overheat LED

Expansion Slots

PCI-Express ■ 4x PCI-E 3.0 x8 Full-height Full-length slots
■ 1x PCI-E 3.0 x8 Low-profile Half-length slot

Drive Bays

Hot-swap ■ 8x 3.5" Hot-swap SATA3 drive bays

Backplane

SAS/SATA HDD Backplane
(SAS support requires optional SAS controller)

System Cooling

Fans ■ 3x 80x80x38mm 7K RPM Cooling fans

Power Supply with Power Distributor

500W high-efficiency redundant power supplies with PMBus

AC Input ■ 100-240 V, 50-60 Hz, 6.1-2.6 Amp

DC Output ■ 4 Amp @ +5V standby
■ 41.7 Amp @ +12V

With Power Distributor ■ +5V: 30 Amp
■ +3.3V: 24 Amp
■ -12V: 0.6 Amp

Certification



Platinum Certified
[[Test Report](#)]

	<ul style="list-style-type: none">■ 1x Realtek RTL8201N PHY (dedicated IPMI)
Video	<ul style="list-style-type: none">■ ASPEED AST2400 BMC
Input / Output	
SATA	<ul style="list-style-type: none">■ 8x SATA3 (6Gbps) ports
LAN	<ul style="list-style-type: none">■ 2x RJ45 Gigabit Ethernet LAN ports■ 1x RJ45 Dedicated IPMI LAN port
USB	<ul style="list-style-type: none">■ 2x USB 2.0 ports (front)■ 2x USB 2.0, 3.0 ports (rear)
Video	<ul style="list-style-type: none">■ 1x VGA port
Serial Port / Header	<ul style="list-style-type: none">■ 1x Fast UART 16550 serial port■ 1x internal header

System BIOS	
BIOS Type	<ul style="list-style-type: none">■ 8MB SPI Flash EEPROM with AMI BIOS
BIOS Features	<ul style="list-style-type: none">■ DMI 2.3■ PCI 2.3■ ACPI 1.0 / 2.0■ USB Keyboard support■ SMBIOS 2.3
Operating Environment / Compliance	
RoHS	<ul style="list-style-type: none">■ RoHS Compliant
Environmental Spec.	<ul style="list-style-type: none">■ Operating Temperature: 10°C to 35°C (50°F to 95°F)■ Non-operating Temperature: -40°C to 70°C (-40°F to 158°F)■ Operating Relative Humidity: 8% to 90% (non-condensing)■ Non-operating Relative Humidity: 5% to 95% (non-condensing)

Parts List

[See Parts List](#)

Terms & Conditions | Privacy | Investor Relations | Jobs | Site Map

SuperServer® | Motherboard | Chassis | Rack Cabinet | SuperBlade® | Embedded | Networking | Storage | Accessories | AMD Solution | Power Supplies

Copyright © 2016 Super Micro Computer, Inc.

Information in this document is subject to change without notice.
Other products and companies referred to herein are trademarks or registered trademarks of their respective companies or mark holders.