


# IFC6410

Snapdragon™ S4 Pro Pico-ITX Single-Board Computer



## High performance, Cost-effective solution based on the Snapdragon S4 Pro chipset

The IFC6410 is an ultra-small, cost-effective single-board computer solution for embedded developers in a convenient Pico-ITX standard form factor. The IFC6410 provides developers access to the rich I/O features of the Snapdragon S4 Pro System-on-Chip at a cost that will not break your budget. The standalone IFC6410 provides quad core A15 class computing in a space-saving footprint with easy access to industry standard I/Os which creates the perfect environment for a variety of unique Android and Linux based multimedia applications including digital signage, thin clients, industrial robotics, and video conferencing.

## Features of Snapdragon APQ8064

- ◆ High Performance A15-class Computing
- ◆ Best-in-class energy efficiency with dedicated power management
- ◆ Best-in-class GPU performance
- ◆ Rich multimedia 1080p capabilities
- ◆ Dedicated DSP for Audio Processing




## Processing, Power, and Performance


- ◆ Qualcomm® Snapdragon™ S4 Pro APQ8064
- ◆ Quad core Krait , 1.7GHz, 2MB L2 cache
- ◆ 2 GB on-board DDR3
- ◆ Independent Clock Scaling Per Core

## Connectivity, Storage & I/O

- ◆ MicroSD card connector, External SATA, eMMC 4GB
- ◆ µHDMI output HD1080p Video
- ◆ Available interface for LVDS-based flat panel and touch screen display
- ◆ HD Audio and Mic-in
- ◆ Supports up to a 20MP Camera MIPI-CSI2
- ◆ Bluetooth 4.0 and Wi-Fi via Atheros QCA6234
- ◆ Standard I/O interfaces including GbE, I2C, SPI, UART, UIM, GPIOs, etc. and on-board Serial Console and USB



## Block Diagram



\* Not all interfaces can be used at the same time

## Technical Specifications

### Processor, GPU, and Memory

- ◆ Qualcomm Snapdragon S4 Pro APQ8064 Quad Core Processor (1.7GHz)
- ◆ 2GB on-board PCDDR3, up to 533MHz
- ◆ Adreno 320 (QXGA/1080p)

### Storage Interfaces

- ◆  $\mu$ SD card connector
- ◆ eMMC 4GB
- ◆ External SATA

### Video, Audio, and I/O Interfaces

- ◆  $\mu$ HDMI for HD1080p
- ◆ LVDS
- ◆ MIPI-CSI2 (4-lane)
- ◆ HD Audio and Mic-in
- ◆ 2x USB 2.0
- ◆ 1x USB OTG
- ◆ Serial Console on 3-pin header
- ◆ 1x I2C
- ◆ 1x SPI
- ◆ 1x UART
- ◆ UIM
- ◆ 8x GPIO

### Network Interfaces

- ◆ 802.11 b/g/n WiFi + Bluetooth 4.0
- ◆ 10/100/1000bps Ethernet

### Power, Mechanical, and Environmental

- ◆ Power: +5V Input Socket (3A typ.)
- ◆ Dimensions: 10cm x 7cm (Pico-ITX)
- ◆ Operating Temp: 0 to 70 C
- ◆ Storage Temp: -20 to 80 C
- ◆ Relative Humidity: 5 to 95% non-condensing
- ◆ RoHS and WEE compliant

### Ordering Info

Part Number	Description	Available
<b>SYS6440-00-P1</b>	Development Kit	NOW
<b>IFC6400-00-P1</b>	Qseven Module	NOW
<b>IFC6410-00-P1</b>	Pico-ITX SBC	NOW

### India Sales & Support

Inforce Computing India Pvt Ltd.  
#24, 3<sup>rd</sup> Floor, 1<sup>st</sup> Cross, Magrath Road  
Bangalore, 560025, India  
Phone: +91 80 2556 6699

[www.inforcecomputing.com](http://www.inforcecomputing.com)



### Corporate Headquarters

Inforce Computing Inc.  
48820 Kato Road Ste 600B,  
Fremont, CA 94538 USA  
Phone: (510) 683-9999  
[sales@inforcecomputing.com](mailto:sales@inforcecomputing.com)