



CONNECTORS

HEADERS & RECEPTACLES



✓ Active

TE CONNECTIVITY (TE)

## EP2.5 HDR ASSY 2P VERT W/O BOSS, TAPING

Economy Power | Economy Power 2.5

2299683-2

TE Internal Number: 2299683-2

EU RoHS Compliant

Not Yet Reviewed for EU ELV

Connector System Wire-to-Board

Number of Positions 2

Centerline (Pitch) 2.5 mm [ .098 in ]

Termination Method to Wire/Cable Solder

PCB Mounting Orientation Vertical

↓ **PRODUCT DRAWING**  
English

↓ **3D PDF**

### DOCUMENTATION

Product Drawings

#### **HEADER ASSEMBLY, VERTICAL ECONOMY POWER, 2.5mm CENTERLINE TAPING VERSION**

PDF

English

CAD Files

**3D PDF**

PDF

**3D**

**Customer View Model**

2D\_DXF.ZIP

English

### Customer View Model

3D\_IGS.ZIP

English

### Customer View Model

3D\_STP.ZIP

English

---

Product Specifications

Application Specification

### Economy Power (EP) 2.5 Contacts; Plug And Receptacle Housings; And Vertical And Right-Angle Headers

PDF

English

Product Specification

### EP 2.5 Connector System

PDF

English

---

Agency Approvals

UL Report

### ECONOMY POWER 2.5 CONNECTOR REPORT

PDF

English

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

### Product Type Features

**Connector System** Wire-to-Board

**PCB Mounting Orientation** Vertical

**Sealable** No

**Connector & Contact Terminates To** Printed Circuit Board

**Product Type** Connector

**Connector Type** Header

**Connector Style** Plug

**Glow Wire Rating** Standard Part - Not Glow Wire

---

### Configuration Features

**Number of Positions** 2

**Number of Rows** 1

**Tail Orientation** Inline

**Selectively Loaded** No

**Backwall/Post Interruptions** Without

---

### Electrical Characteristics

**Operating Voltage (VAC)** 250

---

## Body Features

**Color** Natural

**Header Type** Shrouded

---

## Contact Features

**Contact Mating Area Plating Material** Tin

**Contact Mating Area Plating Thickness** 2.03 µm [ 80 µin ]

**Contact Current Rating (Max) (A)** 4.2

**Contact Style** Straight

**Contact Base Material** Brass

**Contact Layout** Inline

**Contact Termination Area Plating Material** Tin

**Contact Termination Area Plating Thickness (µin)** 80

**Tail Plating Thickness** 2.032 µm [ 80 µin ]

**Contact Transmits (Typical)** Power, Signal (Data)

**Tail Plating Material** Tin

**Contact Design** Round Post

**Contact Shape** Round

**Contact Type** Pin

---

## Termination Features

**Termination Method to Wire/Cable** Solder

**Termination Method to PC Board** Through Hole - Solder

---

## Mechanical Attachment

**PCB Mounting Style** Through Hole

**PCB Mount Alignment** Without

**Mating Retention** With

**PCB Mount Retention** Without

**Mating Alignment** With

**Mating Retention Type** Latch

**Mating Alignment Type** Polarization

**Contact Retention** Without

---

## Housing Features

**Centerline (Pitch)** 2.5 mm [ .098 in ]

**Housing Material** PBT

**Housing Color** Natural

---

## Dimensions

**Height** 8.8 mm [ .346 in ]

**Tail Length** 3.4 mm [ .134 in ]

**Width** 6.4 mm [ .252 in ]

**PCB Thickness (Recommended)** 1.6 mm [ .063 in ]

**Length** 7.5 mm [ .3 in ]

**Mating Post Length** 3.6 mm [ .142 in ]

---

## Usage Conditions

**Operating Temperature Range** -55 – 105 °C [ 131 – 221 °F ]

---

Operation/Application

**Circuit Application** Power

**For Use With** Connector/Cable Assembly

Statement of Compliance

**Statement of Compliance**

PDF