




Home> Products > MICRO SWITCH™ Toggle Switches> TL > Product Page

1TL887-6F



Actual product appearance may vary.

TL Series Toggle Switch, 1 pole, 2 position, Screw terminal, Locking Lever

Features

- Environmentproof sealing
- 1,2, and 4 pole circuitry
- Standard and pull-to-unlock levers
- 2 and 3 position, maintained and momentary toggle action
- Temperature range:-85° F to +160° F
- Completely sealed switching chamber
- Step-design case provides added space between terminals to help prevent shorting
- UL recognized, CSA certified
- CE approved

Potential Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

Description



MICRO SWITCH™TL Series toggle switches have high strength, temperature resistant, non-tracking case material and silver cadmium oxide contacts. Pull-to-Unlock toggle levers prevent accidental operation; the lever must be pulled approx. 2,3 mm (0.09 inches) to change positions.

Supporting Documentation

 [Accessory: Seals](#)

 [Accessory: Nuts](#)

 [Engineering Drawing](#)

Product Specifications	
Circuitry/Operating action	<div>Keyway Momentary Position</div> <div>Opposite Keyway Position</div> 
Product Type	MICRO SWITCH™ Toggle Switch
Lever Lock	 <div>Locked in extreme position (Opposite keyway)</div>
Ampere/Voltage Range (Resistive Load)	0.5 A to 15 A at 0.5 Vdc to 28 Vdc,0.5 A to 10 A at 0.5 Vac to 7 Vac,0.75 A at 115 Vdc,0.5 A at 250 Vdc
Circuitry	SPST
Action	2 position
Mounting	Bushing 15/32 in
Termination	Screw
Lever Type	Locking
UL/CSA Rating Code	L192: 10 A - 125, 250, 277 Vac; 1/4 Hp - 125 Vac; 1/2 Hp - 250, 277 Vac; 3 A - 125 Vac "L"
Comment	Gold Plated Contacts
Availability	Global
UNSPSC Code	30211908
UNSPSC Commodity	30211908 Toggle switches
Series Name	TL

Keyword Search

Search for product and support information.

All Sensing and Control▼

Product Search

Part number search:

Use (*) to expand search

Specification Search