



Over 50 years of engineering innovation 1964-2014

News About Us Contact Us Global Manufacturing Shop Aavid

Products

Solutions

Industries

Know ledge Center

Design Help


简体中文

Register or Sign Into Your Account

Cart

65535

[Back to search results](#)





Height: 2.89 in (73.41 mm)
Width: 12.20 in (309.88 mm)
Weight: 11.3 lb per foot (16.82 kg per meter)
Perimeter: 115.65 in
Material: 6063-T5 Aluminum Extrusion Alloy
RoHS: Compliant. Cut extrusion parts with a G in the part number are compliant.

Thermal Data based on 3 in. length inches in mm



Natural Convection: 0.61 based on 70 C temp rise above ambient

Thermal resistance is calculated based on a single 1" (25.4mm) square heat source centered on the heat sink. If you have distributed loads, then you can expect 10% better performance in natural convection and 20% better performance in forced convection.

Natural Convection



Forced Convection



Not in stock

6-8 weeks lead time

CUSTOM CUT EXTRUSION

SELECT CUT LENGTH:
 IN MM
 FINISH:
 SELECT QUANTITY:
 PIECES
 PART NUMBER: 655353U15000G

EMAIL_ESTORE@AAVID.COM

RAW BAR EXTRUSION

FULL BAR LENGTH:
 UNFINISHED
 SELECT QUANTITY:
 PART NUMBER: 655351F00000



PRICE PER FOOT:

HALF BAR LENGTH:
 UNFINISHED
 SELECT QUANTITY:
 PART NUMBER: 655352F00000

PRICE PER FOOT:

CUSTOMIZE

AAVID OFFERS MANY DIFFERENT OPTIONS FOR YOUR EXTRUSION INCLUDING PUNCHING, DRILLING (CNC), FLY CUTTING, CAUSTIC ETCHING AND MORE.



Customer Assistance

- Contact Us
- Get Design Assistance
- Find a Distributor
- Find a Sales Rep
- Request a Quote
- Placing an Order
- Terms and Conditions
- Returns

Popular Products

- Fans
- Extrusions
- Board Level
- Liquid Cooling
- Heat Pipe Technology
- Heat Sink Accessories
- Interface Materials

Our Company

- News and Events
- Management Team
- Worldwide Locations
- Directions to Headquarters
- Disclaimer
- Customer Survey
- Privacy Policy

Connect with Aavid

Sign up for Aavid News & Alerts

Like / Follow / Connect



© Copyright 2015 Aavid Thermalloy, LLC.

USA: 1.855.32.AAVID Europe: 39.051.764002 Asia: 86.21.6115.2000 x 8122