




Front View



Dawar Tech: FG8_12.1-00001R.B

XXXXXXXXXXXXXXXXXXXX

XXXXXXXXXXXXXXXXXXXX



PIN #	Assignment
1	Left Excite
2	Left Sense
3	Bottom Sense
4	Bottom Excite
5	Right Excite
6	Right Sense
7	Top Sense
8	Top Excite

- NOTES:
1. Operation Temperature: -20°C~+60°C
 - Storage Temperature: -20°C~+70°C
 2. Life Time: >5,000,000 times.
 3. Linearity: ≤ 1.5%
 4. ITO Film: Anatoli-Glare Hard Coating & Anti-Newton Ring
 - Sheet Resistance: 400±50(Ω)/square;
 - ITO Glass: Sheet Resistance: 400±50(Ω)/square
 5. Tail Type: FPC By Golden Plated
 6. All Tolerance Without Marked: ±0.3
 7. All Materials and Components must be RoHS compliant
 8. No Material is allowed to be larger than the glass size

REVISIONS			
REV	DESCRIPTION	DATE	NAME
A	Initial Release.	08-23-07	AMH
B	Updated temp spec and labeling	08-17-09	AMH



1016 North Lincoln Avenue - Pittsburgh, PA 15233-2302
1.800.368.1946 - 412.322.2900 - Fax: 412.322.2959
e-mail: sales@dawar.com - www.dawar.com

THIS DOCUMENT IS THE PROPERTY OF DAWAR TECHNOLOGIES, INC. AND SHALL NOT BE COPIED, REPRODUCED, DISCLOSED, AND/OR USED AS THE BASIS FOR MANUFACTURING OR SALE WITHOUT PERMISSION OF A DULY AUTHORIZED REPRESENTATIVE OF DAWAR TECHNOLOGIES, INC.

CUSTOMER NAME	UNIT	DAWAR PIN	REV
Standard product offering	mm	FG8_12.1-00001	B
CUSTOMER PIN	REV	DRAWN BY	DATE
		Jason Liao	08-17-09
DESCRIPTION	SHEET	MANUFACTURING NO.	REV
12.1" 8-Wire Resistive Touch Screen	1 OF 1		