

# Marvell PXA1088 Pro Quad-core WCDMA/TD-SCDMA Communication Processor

Quad-cortex A7, High-performance, Low-power, Low-cost

## PRODUCT OVERVIEW

The Marvell® PXA1088 Pro is a highly integrated quad-core application and communications mobile System-on-Chip (SoC) that provides high-performance, low-power mobile computing; support for all global broadband 3G standards, enabling seamless global roaming; and the latest wireless connectivity technology. Marvell's PXA1088 Pro is the industry's most advanced single-chip solution to feature a quad-core processor running at 1.5GHz with support for field-proven 3G cellular modems, including High Speed Packet Access Plus (HSPA+), Time Division High Speed Packet Access Plus (TD-HSPA+) and Enhanced Data for GSM Environment (EDGE).

The Marvell PXA1088 Pro solution incorporates the performance of a quad-core ARM® Cortex-A7 with Marvell's mature and proven WCDMA and TD-SCDMA modem technology to provide a low-cost 3G platform for both smartphones and tablets. The advanced application processor technology of the PXA1088 Pro enables a breakthrough end user experience for multimedia and gaming applications with universal connectivity. Marvell's complete mobile platform solution includes the Avastar® 88W8777 WLAN + Bluetooth 4.0 + FM single-chip SoC and the 88L2000 GNSS Hybrid Location Processor, and an integrated power management and audio codec IC.

Marvell's PXA1088 Pro is backward pin-to-pin compatible with its single-chip unified 3G platform family, the quad-core PXA1088 and dual-core PXA988/PXA986, enabling device partners to upgrade their next-generation mobile devices to quad-core without additional design cost.

## FEATURES AND BENEFITS


SPECIAL FEATURES	BENEFITS
<ul style="list-style-type: none"> <li>WCDMA/TD-SCDMA 3G Cellular Modem Solution</li> </ul>	<ul style="list-style-type: none"> <li>Evolution of proven Marvell WCDMA and TD-SCDMA solutions, integrated on leading carrier products, shipping in high volume</li> <li>Marvell PXA1088 Pro high-performance WCDMA/TD-SCDMA platform features:               <ul style="list-style-type: none"> <li>WCDMA HSPA+ (21Mbps), Release 7</li> <li>TD-SCDMA HSPA+ (4.2Mbps), Release 8</li> <li>TD-HSDPA, Release 7</li> <li>Class 12 EDGE support</li> </ul> </li> <li>Fully integrated cellular platform solution with extensive IOT, GCF and carrier field trial testing</li> </ul>
<ul style="list-style-type: none"> <li>Dedicated Modem and Application Processor Subsystems               <ul style="list-style-type: none"> <li>Shared memory hardware architecture</li> <li>Shared external memory interface</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>Enables reuse of a common application processor software stack across multiple air interfaces and cellular networks</li> <li>Prevents unwanted performance interactions/dependencies between AP and modem subsystems</li> <li>Protects cellular network from application processor security threats</li> <li>High-performance internal memory architecture enables sharing of external memory without the cost and space burden for independent Flash and DDR</li> <li>High-performance, efficient inter-processor communication interface between AP and modem, using shared external DDR</li> </ul>
<ul style="list-style-type: none"> <li>Efficient, Proven Modem Processors               <ul style="list-style-type: none"> <li>Modem RISC core</li> <li>Modem DSP core</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>Marvell-designed ARM9 with packet processing accelerators and L1/L2 caches</li> <li>Micro Signal Architecture VLIW DSP core with L1/L2 caches</li> </ul>

## FEATURES AND BENEFITS continued

SPECIAL FEATURES	BENEFITS
<ul style="list-style-type: none"> <li>Quad ARM Cortex A7MP Application Processor Subsystem</li> </ul>	<ul style="list-style-type: none"> <li>A high-performance quad-core ARM Cortex A7 for low-power applications, with high-performance for browsing and Java applets</li> <li>NEON™ engine for broad support of media codecs</li> <li>High-performance memory support for LPDDR2-SDRAM, DDR3/L, NAND and eMMC; secure boot from NAND and eMMC</li> <li>Support mobile security features, including secure boot, root key protection and Widevine® Level 1 support</li> </ul>
<ul style="list-style-type: none"> <li>Full HW-Supported Multimedia Suite               <ul style="list-style-type: none"> <li>- Video decode and encode</li> <li>- 3D graphics</li> <li>- Audio</li> <li>- Imaging</li> <li>- Display</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>Video decode: 1080p 30 fps/720p 60 fps, with support for H.263, H.264 HP,</li> <li>MPEG-4, MPEG 2, DivX/XviD, AVS and RV</li> <li>Video capture: 1080p 30 fps, with support for H.263, H.264 and MPEG-4</li> <li>MJPEG encode and decode, maximum resolution 8192x8192</li> <li>3D graphics capability up to 96 Mtriangles/s peak rate and 1.56 Gpixels/s peak fill rate; integrated 2D accelerator; supports industry standard APIs, OpenGL ES 2.0/1.1 and Open VG 1.1</li> <li>Low-power audio playback with direct streaming from external source to internal SRAM</li> <li>Imaging sensor support for primary and secondary sensors with one CSI-4 port, up to 4 data lanes (1Gb/s per lane)</li> <li>Integrated ISP supports up to 12 Mpixel sensor</li> <li>LCD controller supports 1 MIPI DSI port (4 lanes) with up to 720p resolution</li> <li>Up to 4 simultaneous overlays</li> </ul>

## APPLICATIONS

This highly integrated handset platform features the PXA1088 Pro single-chip applications and baseband processor, with a Marvell integrated power management and audio companion IC, and Marvell 802.11n WLAN/BT/FM.



Marvell PXA1088 Pro SoC (not actual size)

**THE MARVELL ADVANTAGE:** Marvell chipsets come with complete reference designs which include board layout designs, software, manufacturing diagnostic tools, documentation, and other items to assist customers with product evaluation and production. Marvell's worldwide field application engineers collaborate closely with end customers to develop and deliver new leading-edge products for quick time-to-market. Marvell utilizes world-leading semiconductor foundry and packaging services to reliably deliver high-volume and low-cost total solutions.

**ABOUT MARVELL:** Marvell (NASDAQ: MRVL) is a global leader in providing complete silicon solutions enabling the digital connected lifestyle. From mobile communications to storage, cloud infrastructure, digital entertainment and in-home content delivery, Marvell's diverse product portfolio aligns complete platform designs with industry-leading performance, security, reliability and efficiency. At the core of the world's most powerful consumer, network and enterprise systems, Marvell empowers partners and their customers to always stand at the forefront of innovation, performance and mass appeal. By providing people around the world with mobility and ease of access to services adding value to their social, private and work lives, Marvell is committed to enhancing the human experience. As used herein, the term "Marvell" refers to Marvell Technology Group Ltd. and its subsidiaries.

**CONTACT US:** For additional information, please visit our website at [www.marvell.com](http://www.marvell.com) for a Marvell sales office or representative in your area.



Marvell Technology Group  
[www.marvell.com](http://www.marvell.com)