

# Double Row Terminal Blocks

## 200HB Series (High Barrier)

### 600 Volts AC/DC (Class C)

(See page 86 for Thermoplastic Version 621 RZ)



206HB

### Specifications:

- Base, General Purpose Phenolic, 150°C
- Closed Back Design
- Screws, #6-32 Binder Head, Phil-Slot, Steel
- Terminals, Plated Brass
- 1-30 Poles
- 7/16" Centers
- Wire Range With Wire Binding Screw #12 - #22 AWG – 20 Amps
- Wire Range With Sems Pressure Screw #12 - #22 AWG Stranded Copper Wire Only, 20 Amps
- UL Recognized File No. XCFR2.E62806
- CSA Certified File No. LR19766
- **CE**
- RoHS Compliant

MSP Catalog #	# of poles	Dimensions	
		A	B
201HB	1	1.19	0.88
202HB	2	1.62	1.31
203HB	3	2.06	1.75
204HB	4	2.50	2.19
205HB	5	2.94	2.63
206HB	6	3.37	3.06
207HB	7	3.81	3.50
208HB	8	4.25	3.94
209HB	9	4.69	4.38
210HB	10	5.12	4.81
211HB	11	5.56	5.25
212HB	12	6.00	5.69
213HB	13	6.44	6.13
214HB	14	6.87	6.56
215HB	15	7.31	7.00
216HB	16	7.75	7.44
217HB	17	8.19	7.88
218HB	18	8.62	8.31
219HB	19	9.06	8.75
220HB	20	9.50	9.19
221HB	21	9.94	9.63
222HB	22	10.37	10.06
223HB	23	10.81	10.50
224HB	24	11.25	10.94
225HB	25	11.69	11.38
226HB	26	12.12	11.81
227HB	27	12.56	12.25
228HB	28	13.00	12.69
229HB	29	13.44	13.13
230HB	30	13.87	13.56

mm=dim X 25.4

For electronic drawings or 2D/3D CAD data, send request to [drawings@marathonsp.com](mailto:drawings@marathonsp.com)

### Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

CATALOG #	PRODUCT DESCRIPTION	PAGE REFERENCE	
F1	Full Quick Connect (0° Flat)	See page 101	
F2	Full Quick Connect (45° Bend)	See page 101	
F3	Full Quick Connect (90° Bend)	See page 101	
HF1	Half Quick Connect (0° Flat)	See page 101	
HF2	Half Quick Connect (45° Bend)	See page 101	
HF3	Half Quick Connect (90° Bend)	See page 101	
S	Full Solder	See page 102	
HS	Half Solder	See page 102	
L	Y	Feed Thru Solder (.437)	See page 102
LSL	YSY	Feed Thru Solder (.625)	See page 102
LL 200HB	Line to Line Jumper	See page 103	
	601RJ(S)	Multiple Position Jumper	See page 103
SP	SEMS Pressure Saddle Screw	See page 103	
SPSE	SEMS Pressure Saddle Screw with External Tooth Lock Washer	Consult C/S	
LWW	Feed Thru Wire Wrap (.640)	Consult C/S	
PSB	Phil-Slot Brass Screw	Consult C/S	

Quick Connects: .032" x .250"

See pages 100-111 for terminal block accessories

