

Specification Sheet

Part Number: PR1M4



Panel Rivet, PA66, Natural, 1000/bag

Article Number	181-00139
Type	PR1
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">• Panel rivets are made with nylon material to hold duct securely to the panel without corroding, ensuring longevity.• Panel rivets can be easily inserted with use of a specially designed, long shafted panel rivet tool.• Ergonomic design of the tool ensures effortless use when inserting rivets into deep channels or locations difficult to access.
Quantity Per	EA

Product Description	HellermannTyton panel rivets are one piece drive rivets that provide a fast, economic means of affixing wiring duct. The rivet is inserted into a 3/16" pre-punched hole and the pin is driven into the base, thereby expanding the rivet legs and locking the duct and sub-panel in place. The panel thickness (including the duct thickness) should be a maximum of 3/16".
Short Description	Panel Rivet, PA66, Natural, 1000/bag
Global Part Name	PR1-PA66-NA
Technical Description	Panel Rivet
Minimum Tensile Strength (Imperial)	107.0
Minimum Tensile Strength (Metric)	478
Panel Thickness Min(Imperial)	0.15
Panel Thickness Max(Imperial)	0.28
Panel Thickness Min (Metric)	3.9
Panel Thickness Max (Metric)	7.0
Mounting Hole Diameter D (Imperial)	0.2
Mounting Hole Diameter D (Metric)	5.0 mm
Mounting Hole Diameter D Max (Metric)	5.0

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 HB
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +176°F (-40°C to +80°C)
Reach Complaint(Article 33)	No
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

© 2020 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)