

SCHOTTKY RECTIFIER
HIGH EFFICIENCY SERIES

80SCLQ045

80 Amp, 45V


Major Ratings and Characteristics

Characteristics	80SCLQ045	Units
$I_{F(AV)}$	80	A
V_{RRM} (Per Leg)	45	V
I_{FSM} @ $t_p = 8.3ms$ half-sine (Per Leg)	250	A
V_F @ $40A_{pk}$, $T_J = 125^\circ C$ (Per Leg)	0.62	V
T_J , T_{stg} Operating and storage	-55 to 150	$^\circ C$

Description/Features

The 80SCLQ045 center tap Schottky rectifier has been expressly designed to meet the rigorous requirements of hi-rel environments. It is packaged in the hermetic surface mount SMD-1 ceramic package. The device's forward voltage drop and reverse leakage current are optimized for the lowest power loss and the highest circuit efficiency for typical high frequency switching power supplies and resonant power converters. Full MIL-PRF-19500 quality conformance testing is available on source control drawings to TX, TXV and S quality levels.

- Hermetically Sealed
- Center Tap
- Low Forward Voltage Drop
- High Frequency Operation
- Guard Ring for Enhanced Ruggedness and Long term Reliability
- Surface Mount
- Lightweight



80SCLQ045

International
IOR Rectifier**Voltage Ratings**

Part number	80SCLQ045
V _R Max. DC Reverse Voltage (V) (Per Leg)	45
V _{RWM} Max. Working Peak Reverse Voltage (V) (Per Leg)	

Absolute Maximum Ratings

Parameters	Limits	Units	Conditions
I _{F(AV)} Max. Average Forward Current See Fig. 5	80	A	50% duty cycle @ T _C = 84°C, square waveform
I _{FSM} Max. Peak One Cycle Non - Repetitive Surge Current (Per Leg)	250	A	@ t _p = 8.3 ms half-sine

Electrical Specifications

Parameters	Limits	Units	Conditions
V _{FM} Max. Forward Voltage Drop (Per Leg) See Fig. 1①	0.62	V	@ 30A
	0.67	V	@ 40A
	0.70	V	@ 45A
	0.85	V	@ 80A
	0.57	V	@ 30A
	0.63	V	@ 40A
	0.66	V	@ 45A
	0.88	V	@ 80A
	0.53	V	@ 30A
	0.62	V	@ 40A
	0.64	V	@ 45A
	0.87	V	@ 80A
I _{RM} Max. Reverse Leakage Current (Per Leg) See Fig. 2①	0.6	mA	T _J = 25°C
	80	mA	T _J = 100°C
	195	mA	T _J = 125°C
C _T Max. Junction Capacitance (Per Leg)	2000	pF	V _R = 5V _{DC} (1MHz, 25°C)
L _S Typical Series Inductance (Per Leg)	5.9	nH	Measured from center of cathode pad to center of anode pad

Thermal-Mechanical Specifications

Parameters	Limits	Units	Conditions
T _J Max. Junction Temperature Range	-55 to 150	°C	
T _{stg} Max. Storage Temperature Range	-55 to 150	°C	
R _{thJC} Max. Thermal Resistance, Junction to Case (Per Leg)	1.25	°C/W	DC operation See Fig. 4
R _{thJC} Max. Thermal Resistance, Junction to Case (Per Package)	0.63	°C/W	DC operation
wt Weight (Typical)	2.6	g	
Die Size (Typical)	150X180	mils	
Case Style	SMD-1		

① Pulse Width < 300μs, Duty Cycle < 2%




Fig. 1 - Max. Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values of Reverse Current Vs. Reverse Voltage (Per Leg)






Fig. 3 - Typical Junction Capacitance Vs. Reverse Voltage (Per Leg)

Fig. 4 - Max. Thermal Impedance Z_{thJC} Characteristics (Per Leg)Fig. 5 - Max. Allowable Case Temperature Vs.
Average Forward Current (Per Leg)International
IOR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
IR EUROPEAN REGIONAL CENTRE: 439/445 Godstone Rd, Whyteleafe, Surrey CR3 0BL, UK Tel: ++ 44 (0)20 8645 8000
IR CANADA: 15 Lincoln Court, Brampton, Ontario L6T3Z2, Tel: (905) 453 2200
IR GERMANY: Saalburgstrasse 157, 61350 Bad Homburg Tel: ++ 49 (0) 6172 96590
IR ITALY: Via Liguria 49, 10071 Borgaro, Torino Tel: ++ 39 011 451 0111
IR JAPAN: K&H Bldg., 2F, 30-4 Nishi-Ikebukuro 3-Chome, Toshima-Ku, Tokyo 171 Tel: 81 (0)3 3983 0086
IR SOUTHEAST ASIA: 1 Kim Seng Promenade, Great World City West Tower, 13-11, Singapore 237994 Tel: ++ 65 (0)838 4630
IR TAIWAN: 16 Fl. Suite D. 207, Sec. 2, Tun Haw South Road, Taipei, 10673 Tel: 886-(0)2 2377 9936
Data and specifications subject to change without notice. 10/00