

# Switch-mode Power Rectifier

## DPAK Surface Mount Package

### MBRD835L, SBRD8835L

This switch-mode power rectifier which uses the Schottky Barrier principle with a proprietary barrier metal, is designed for use as output rectifiers, free wheeling, protection and steering diodes in switching power supplies, inverters and other inductive switching circuits.

#### Features

- Low Forward Voltage
- 150 °C Operating Junction Temperature
- Epoxy Meets UL 94 V-0 @ 0.125 in
- Compact Size
- Lead Formed for Surface Mount
- SBRD8 Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant


#### Mechanical Characteristics

- Case: Epoxy, Molded
- Weight: 0.4 Gram (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes: 260 °C Max. for 10 Seconds
- Shipped 75 Units Per Plastic Tube
- ESD Rating:
  - ♦ Machine Model = C (> 400 V)
  - ♦ Human Body Model = 3B (> 8000 V)


## SCHOTTKY BARRIER RECTIFIER 8.0 AMPERES, 35 VOLTS



DPAK  
CASE 369C



#### MARKING DIAGRAM



B835LG = Specific Device Number  
A = Assembly Location\*  
Y = Year  
WW = Work Week  
G = Pb-Free Device

\* The Assembly Location Code (A) is front side optional. In cases where the Assembly Location is stamped in the package bottom (molding ejector pin), the front side assembly code may be blank.

#### ORDERING INFORMATION

| Device            | Package           | Shipping <sup>†</sup> |
|-------------------|-------------------|-----------------------|
| MBRD835LT4G       | DPAK<br>(Pb-Free) | 2500 /<br>Tape & Reel |
| SBRD8835LT4G-VF01 | DPAK<br>(Pb-Free) | 2500 /<br>Tape & Reel |

<sup>†</sup> For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, [BRD8011/D](#).

# MBRD835L, SBRD8835L

## MAXIMUM RATINGS

| Rating                                                                                                                    | Symbol                          | Value       | Unit               |
|---------------------------------------------------------------------------------------------------------------------------|---------------------------------|-------------|--------------------|
| Peak Repetitive Reverse Voltage<br>Working Peak Reverse Voltage<br>DC Blocking Voltage                                    | $V_{RRM}$<br>$V_{RWM}$<br>$V_R$ | 35          | V                  |
| Average Rectified Forward Current<br>( $T_C = 88\text{ }^{\circ}\text{C}$ )                                               | $I_{F(AV)}$                     | 8.0         | A                  |
| Peak Repetitive Forward Current<br>(Square Wave, Duty = 0.5, $T_C = 80\text{ }^{\circ}\text{C}$ )                         | $I_{FRM}$                       | 16          | A                  |
| Non-Repetitive Peak Surge Current<br>(Surge applied at rated load conditions, halfwave, single phase, 60 Hz)              | $I_{FSM}$                       | 75          | A                  |
| Repetitive Avalanche Current<br>(Current Decaying Linearly to Zero in 1 $\mu\text{s}$ , Frequency Limited by $T_{Jmax}$ ) | $I_{AR}$                        | 2.0         | A                  |
| Storage / Operating Case Temperature                                                                                      | $T_{stg}$                       | -65 to +150 | $^{\circ}\text{C}$ |
| Operating Junction Temperature (Note 1)                                                                                   | $T_J$                           | -65 to +150 | $^{\circ}\text{C}$ |
| Voltage Rate of Change (Rated $V_R$ )                                                                                     | $dv/dt$                         | 10,000      | V/ $\mu\text{s}$   |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. The heat generated must be less than the thermal conductivity from Junction-to-Ambient:  $dP_D/dT_J < 1/R_{\theta JA}$ .

## THERMAL CHARACTERISTICS

| Characteristic                                    | Symbol          | Value | Unit                 |
|---------------------------------------------------|-----------------|-------|----------------------|
| Thermal Resistance – Junction-to-Case             | $R_{\theta JC}$ | 2.8   | $^{\circ}\text{C/W}$ |
| Thermal Resistance – Junction-to-Ambient (Note 2) | $R_{\theta JA}$ | 80    | $^{\circ}\text{C/W}$ |

2. Rating applies when surface mounted on the minimum pad size recommended.

## ELECTRICAL CHARACTERISTICS

| Characteristic                                                                                                                                                                        | Symbol | Value        | Unit |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|--------------|------|
| Maximum Instantaneous Forward Voltage (Note 3)<br>( $I_F = 8\text{ Amps}$ , $T_C = +25\text{ }^{\circ}\text{C}$ )<br>( $I_F = 8\text{ Amps}$ , $T_C = +125\text{ }^{\circ}\text{C}$ ) | $V_F$  | 0.51<br>0.41 | V    |
| Maximum Instantaneous Reverse Current (Note 3)<br>(Rated dc Voltage, $T_C = +25\text{ }^{\circ}\text{C}$ )<br>(Rated dc Voltage, $T_C = +100\text{ }^{\circ}\text{C}$ )               | $I_R$  | 1.4<br>35    | mA   |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. Pulse Test: Pulse Width = 300  $\mu\text{s}$ , Duty Cycle  $\leq 2\%$ .



TYPICAL CHARACTERISTICS




Figure 1. Maximum Forward Voltage




Figure 2. Typical Forward Voltage




Figure 3. Maximum Reverse Current




Figure 4. Typical Reverse Current

# MBRD835L, SBRD8835L

## TYPICAL CHARACTERISTICS




Figure 5. Maximum and Typical Capacitance




Figure 6. Current Derating, Infinite Heatsink




Figure 7. Current Derating




Figure 8. Current Derating, Free Air




Figure 9. Forward Power Dissipation


## MBRD835L, SBRD8835L

### REVISION HISTORY

| Revision | Description of Changes                                                                                                                                  | Date       |
|----------|---------------------------------------------------------------------------------------------------------------------------------------------------------|------------|
| 14       | MBRD835LG, SBRD8835LG, SBRD8835LG-VF01, SBRD835LT4G-VF01, SBRD8835LT4G<br>OPN Marked as Discontinued + Rebranded the Data Sheet to <b>onsemi</b> format | 7/4/2025   |
| 15       | Removal of discontinued devices (MBRD835LG, SBRD8835LG, SBRD8835LG-VF01,<br>SBRD835LT4G-VF01, SBRD8835LT4G) from the data sheet                         | 12/16/2025 |

This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.








DPAK-3 6.10x6.54x2.28, 2.29P  
CASE 369C  
ISSUE L

DATE 24 AUG 2026





SCALE 1:1



| MILLIMETERS |          |      |       |
|-------------|----------|------|-------|
| DIM         | MIN      | NOM  | MAX   |
| A           | 2.18     | 2.28 | 2.38  |
| A1          | 0.00     | ---  | 0.13  |
| b           | 0.63     | 0.76 | 0.89  |
| b2          | 0.72     | 0.93 | 1.14  |
| b3          | 4.57     | 5.02 | 5.46  |
| c           | 0.46     | 0.54 | 0.61  |
| c2          | 0.46     | 0.54 | 0.61  |
| D           | 5.97     | 6.10 | 6.22  |
| E           | 6.35     | 6.54 | 6.73  |
| e           | 2.29 BSC |      |       |
| H           | 9.40     | 9.91 | 10.41 |
| L           | 1.40     | 1.59 | 1.78  |
| L1          | 2.90 REF |      |       |
| L2          | 0.51 BSC |      |       |
| L3          | 0.89     | ---  | 1.27  |
| L4          | ---      | ---  | 1.01  |
| Z           | 3.93     | ---  | ---   |





BOTTOM VIEW



ALTERNATE CONSTRUCTIONS

NOTES:

1. DIMENSIONING AND TOLERANCING ASME Y14.5M, 2018.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSIONS b3, L3, AND Z.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS.
5. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
6. DATUMS A AND B ARE DETERMINED AT DATUM PLANE H.
7. OPTIONAL MOLD FEATURE.



RECOMMENDED MOUNTING FOOTPRINT\*  
\*For additional information on our Pb-Free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques reference manual, SOLDERM/D.


|                  |                              |                                                                                                                                                                                     |
|------------------|------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98AON10527D                  | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | DPAK-3 6.10x6.54x2.28, 2.29P | PAGE 1 OF 2                                                                                                                                                                         |

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**DPAK–3 6.10x6.54x2.28, 2.29P**  
CASE 369C  
ISSUE L

DATE 24 AUG 2026

**GENERIC  
MARKING DIAGRAM\***



XXXXXX = Device Code  
A = Assembly Location  
L = Wafer Lot  
Y = Year  
WW = Work Week  
G = Pb–Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb–Free indicator, “G” or microdot “▪”, may or may not be present. Some products may not follow the Generic Marking.

|                                                                              |                                                                              |                                                                         |                                                                                   |                                                                          |
|------------------------------------------------------------------------------|------------------------------------------------------------------------------|-------------------------------------------------------------------------|-----------------------------------------------------------------------------------|--------------------------------------------------------------------------|
| <b>STYLE 1:</b><br>PIN 1. BASE<br>2. COLLECTOR<br>3. EMITTER<br>4. COLLECTOR | <b>STYLE 2:</b><br>PIN 1. GATE<br>2. DRAIN<br>3. SOURCE<br>4. DRAIN          | <b>STYLE 3:</b><br>PIN 1. ANODE<br>2. CATHODE<br>3. ANODE<br>4. CATHODE | <b>STYLE 4:</b><br>PIN 1. CATHODE<br>2. ANODE<br>3. GATE<br>4. ANODE              | <b>STYLE 5:</b><br>PIN 1. GATE<br>2. ANODE<br>3. CATHODE<br>4. ANODE     |
| <b>STYLE 6:</b><br>PIN 1. MT1<br>2. MT2<br>3. GATE<br>4. MT2                 | <b>STYLE 7:</b><br>PIN 1. GATE<br>2. COLLECTOR<br>3. EMITTER<br>4. COLLECTOR | <b>STYLE 8:</b><br>PIN 1. N/C<br>2. CATHODE<br>3. ANODE<br>4. CATHODE   | <b>STYLE 9:</b><br>PIN 1. ANODE<br>2. CATHODE<br>3. RESISTOR ADJUST<br>4. CATHODE | <b>STYLE 10:</b><br>PIN 1. CATHODE<br>2. ANODE<br>3. CATHODE<br>4. ANODE |

|                  |                              |                                                                                                                                                                                     |
|------------------|------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98AON10527D                  | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red. |
| DESCRIPTION:     | DPAK–3 6.10x6.54x2.28, 2.29P | PAGE 2 OF 2                                                                                                                                                                         |

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

