



Catalog No. TY25M-6

Description: CABLE TIE 50LB 7IN BLUE NYLON

UPC No 786210844893

Home > Wire & Cable Management > Ty-Rap > Cable ties

High Performance Cable Tie for Indoor applications, Blue Color Nylon 6.6, Length of 186mm (7.3 Inches) for Bundle Diameter up to 48mm (1.89 Inches), Width of 4.9mm (0.19 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Military Specified (MIL-SPEC MS3367-1-6), Bulk Pack

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Blue
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds , 222 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405

Dimensions

Width	0.19 in , 4.9 mm
Length	7.2 in , 183 mm
Thickness	0.05 in , 1.3 mm
Bundle Diameter	0.12 to 1.89 in , 3 to 48 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant

ETIM Classification

ETIM	EC000046 Cable tie
Band width	4.9 mm

by ABB

ETIM	EC000046 Cable tie
Band width	0.19 inch
Length belt/tape/tie	183 mm
Length belt/tape/tie	7.2 inch
Tie thickness	1.3 mm
Tie thickness	0.05 inch
Max. bundle diameter	48 mm
Max. bundle diameter	1.89 inch
Min. holding force	222 N
Operation temperature	-60-+85 °C
Operation temperature	-76-+185 °F
Model	Internal tothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Blue
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y