

MICRO SWITCH
FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL INC.
FED. MFG. CODE 91929

SWITCH-ENCLOSED

CATALOG LISTING
2VBI





NOTES
1 - UNIT INCLUDES (2) CAT. LIST. V3-1001 BASIC SWITCH (MS25253-1)
2 - ALUMINUM ENCLOSURE ZINC PHOSPHATE COATED AND FINISHED WITH ONE COAT PRIMER
3 - SWITCH WILL PERFROM SATISFACTORILY IN TEMPERATURES TO MINUS 65°F
4 - SWITCHES DO NOT OPERATE SIMULTANEOULSY

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS

OPERATING FORCE ----- 5 LBS MAX
RELEASE FORCE ------- 1/2 LB MIN
DIFFERENTIAL TRAVEL ---- .031 MAX
OVERTRAVEL ---------- .250 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T (2)

10 AMPS RES. 10 AMPS IND. (SEA LEVEL)
6 AMPS IND. (50,000 FT)
6 AMPS MOTOR LOAD, 30 VDC

SCALE FULL — DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT .27 LB

REPLACES
RELEASE NO. M 2VBI
DRAWING NUMBER M12
ISSUE
CHECK

REVISIONS

A	C063567	WJM 13 MAY 88
B	204536	JAH 12 DEC 01

CHECK D J S 24 MAY 88
CHECK
CHECK
DRAWN JM 13 MAY 88
RASTER

Downloaded from Arrow.com.