

1528280

https://www.phoenixcontact.com/us/products/1528280

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 5-position, Socket, straight, M12-SPEEDCON, coding: A, Rear mounting, THR solder connection, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Commercial data

| Item number | 1528280 |
|--------------------------------------|--------------------------------|
| Packing unit | 100 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | AB23 |
| Product key | ABQAGS |
| Catalog page | Page 28 (PC-2007) |
| GTIN | 4046356023252 |
| Weight per piece (including packing) | 8.27 g |
| Weight per piece (excluding packing) | 8.074 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |



1528280

https://www.phoenixcontact.com/us/products/1528280

Technical data

Mounting type

Mounting

| 2 |
|---|
| 2 |

Rear mounting

Material specifications

| Flammability rating according to UL 94 | НВ |
|--|------|
| Seal material | FKM |
| Contact material | CuZn |
| Contact surface material | Au |

Electrical properties

| Contact resistance | ≤ 0.003 Ω |
|--------------------------------|-----------|
| Insulation resistance | ≥ |
| Nominal voltage U _N | 60 V |
| Nominal current I _N | 4 A |

Connection data

Conductor connection

| Connection method | THR solder connection |
|-------------------------|-----------------------|
| Contact connection type | Socket |

Connector

Connection 1

| Head design | Socket | |
|-------------------|----------|--|
| Head cable outlet | straight | |
| Head thread type | M12 | |
| Head locking type | SPEEDCON | |
| Coding | A | |

Environmental and real-life conditions

Ambient conditions



1528280

https://www.phoenixcontact.com/us/products/1528280


| Degree of protection | IP67 |
|---------------------------------|--------------------------|
| | IP67 |
| Ambient temperature (operation) | -25 °C 85 °C |
| UL Type Rating | Type 4 (indoor use only) |



1528280

https://www.phoenixcontact.com/us/products/1528280

Drawings



Pin assignment M12 socket, 5-pos., A-coded, socket side view



1528280

https://www.phoenixcontact.com/us/products/1528280

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1528280

| .71 | cUL Recognized Approval ID: E118976 | | | | |
|-----|--|-----------------------|--------------------------------|-------------------|-------------------------------|
| | | Nominal voltage U_N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| | | 120 V | 4 A | - | - |

| 71 | UL Recognized Approval ID: E118976 | | | | |
|-----------|---|--------------------------------|--------------------------------|-------------------|-------------------------------|
| | | Nominal voltage U _N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| | | 120 V | 4 A | - | - |



1528280

https://www.phoenixcontact.com/us/products/1528280

Classifications

UNSPSC 21.0

| _ | \sim | Δ | C | C |
|---|--------|---|-----|------|
| _ | | ч | . つ | . `` |

| | ECLASS-13.0 | 27440110 |
|----|-------------|----------|
| ΕΊ | ТІМ | |
| | ETIM 9.0 | EC003568 |
| U | NSPSC | |

39121400



1528280

https://www.phoenixcontact.com/us/products/1528280

Environmental product compliance

EU RoHS

| Fulfills EU RoHS substance requirements | Yes, No exemptions | |
|---|--|--|
| China RoHS | | |
| Environment friendly use period (EFUP) | EFUP-E | |
| | No hazardous substances above the limits | |
| EU REACH SVHC | | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% | |

Phoenix Contact 2025 © - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com