Part Number : 1200980024
Product Description : Micro-Change (M12) Double-Ended Cordset, 5 Poles, B-Coded, Female (Straight) to Male (90°), 24 AWG, 1.0m (3.28') Length, PROFIBUS PUR Cable Preferred Version in Europe
Series Number : 120098
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : BB5S32PP4M010



Documents and Resources

Drawings

1200980024_sd.pdf

Specifications

TS-120065-004-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120098
Description	Micro-Change (M12) Double-Ended Cordset, 5 Poles, B-Coded, Female (Straight) to Male (90°), 24 AWG, 1.0m (3.28') Length, PROFIBUS PUR Cable Preferred Version in Europe
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	EtherNet
Type	Double Ended
UPC	78678852057

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC/DC

Physical

Cable Diameter	8.00mm (.315")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Violet
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded

Downloaded from Arrow.com.

Gender	Female-Male
Keyway	B-Coded
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	1.000/g
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Twisted Pair
Wire Size (AWG)	24

Downloaded from Arrow.com.