



Part Number : [1200720305](#)

Product Description : Micro-Change (1/2"-20 UNF) Single-Ended Cordset, 3 Poles, C-Coded, Male (Straight) to Pigtail, 22 AWG, Yellow PVC Cable, 3.66m (12.0') Length

Series Number : 120072

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 703006D02F120



Documents and Resources

Drawings

[1200720305_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120072
Description	Micro-Change (1/2"-20 UNF) Single-Ended Cordset, 3 Poles, C-Coded, Male (Straight) to Pigtail, 22 AWG, Yellow PVC Cable, 3.66m (12.0') Length
IP Rating	IP67
Product Name	Micro-Change (1/2" - 20 UNF)
Protocol	PROFIBUS
Type	Single Ended
UPC	78678831540

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	5.72mm (.225")
Cable Length	3.66m (12.0')
Color - Cable Jacket	Yellow
Connector End A	Micro-Change (1/2" - 20 UNF)

Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	C-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - O-Ring	Nitrile Rubber
Material - Plating Mating	Gold
Net Weight	77.000/g
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 2661
Wire Size (AWG)	22

This document was generated on Dec 29, 2025