TRACO POWER

AC/DC Medical Power Supply

TMF 30 Series, 30 Watt

- **Fully encapsulated power supplies in plasic casing for PCB mount**
- **Certification according to IEC/EN/ES 60601-1 edition 3.2 for 2xMOPP**
- **Risk management process according to ISO 14971 incl. risk management file**
- **Acceptance criteria for electronic assemblies acc. to IPC-A-610 Level 3**
- **Low leakage current <100 µA rated for BF applications**
- **Operating temperature range: –25°C to +70°C max.**
- **Protection against short-circuit, over load and over voltage**
- **Protection class II prepared**
- **5-year product warranty**



ES 60601-1 IEC 60601-1

The TMF 30 Series AC/DC power supply modules are designed and manufactured based on workmanship standards and risk management to comply with the requirements for quality, reliability and safety of medical equipment. The units are approved to IEC/EN/ES 60601-1 edition 3.2 for 2 x MOPP (Means Of Patient Protection) and come along with an ISO 14971 risk management file. These fully encapsulated modules are for PCB mount. They are designed for protection class II applications (no earth connection) and feature a low leakage current (<100 µA). A compact design and excellent EMC considerations facilitate the design in. The thermal management enables an operation within a wide temperature range of -25 to +70°C and the isolation system is designed and approved for an altitude of 5000 m (AMSL). This makes the power supplies suitable not only for stationary applications but also for transportable medical equipment.

Models

Order Code	Output Power max.	Output Voltage nom.	Output Current max.	Efficiency typ.
TMF 30105	25 W	5 VDC	5'000 mA	82 %
TMF 30112	30 W	12 VDC	2'500 mA	88 %
TMF 30115		15 VDC	2'000 mA	86 %
TMF 30124		24 VDC	1'250 mA	85 %

Downloaded from Arrow.com.

Input Specifications

Input Voltage	- AC Range	Operational Range:	90 - 264 VAC (Full Range)
		Rated Range:	100 - 240 VAC (Full Range)
	- DC Range	Operational Range:	120 - 370 VDC (Designed for, no certification)
		Polarity:	irrelevant
Input Frequency		Operational Range:	47 - 440 Hz
		Certified:	50/60 Hz
Power Consumption	- No load & Vin = 230 VAC		150 mW max. (Ready to meet ErP directive)
	- No load & Vin = 115 VAC		150 mW max.
Input Current	- Full load & Vin = 230 VAC		440 mA max.
	- Full load & Vin = 115 VAC		770 mA max.
Input Inrush Current	- At 230 VAC		60 A max.
	- At 115 VAC		30 A max.
Recommended Input Fuse			(The need of an external fuse has to be assessed in the final application.)

Output Specifications

Voltage Set Accuracy			±2% max.
Regulation	- Input Variation (Vmin - Vmax)		0.5% max.
	- Load Variation (0 - 100%)		1% max.
Ripple and Noise (20 MHz Bandwidth)		5 VDC model:	100 mVp-p max.
		12 VDC model:	120 mVp-p max.
		15 VDC model:	150 mVp-p max.
		24 VDC model:	240 mVp-p max.
Capacitive Load		5 VDC model:	6'800 µF max.
		12 VDC model:	1'600 µF max.
		15 VDC model:	1'200 µF max.
		24 VDC model:	470 µF max.
Minimum Load			Not required
Temperature Coefficient			±0.05 %/K max.
Hold-up Time	- At 230 VAC		45 ms min.
	- At 115 VAC		14 ms min.
Short Circuit Protection			Continuous, Automatic recovery
Output Current Limitation			115 - 215% of Iout max.
Overvoltage Protection			105 - 145% of Vout nom. (By Zener diode)

Safety Specifications

Standards	- Medical Equipment		EN 60601-1 IEC 60601-1 ANSI/AAMI ES 60601-1 CSA-C22.2, No 60601-1 2 x MOPP (Means Of Patient Protection)
	- Certification Documents		www.tracopower.com/overview/tmf30
Protection Class			Class I & II (Prepared): Reinforced Insulation
		See application note:	www.tracopower.com/info/protection-class.pdf
Pollution Degree			PD 2
Over Voltage Category			OVC II

EMC Specifications

EMI (Emissions)		EN 60601-1-2 edition 4 (Medical Devices)
	- Conducted Emissions	EN 55011 class A (internal filter)
		EN 55011 class B (internal filter)
	- Radiated Emissions	EN 55011 class A (internal filter)
		EN 55011 class B (internal filter)

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Downloaded from Arrow.com.

EMS (Immunity)			EN 61000-6-2 (Generic Industrial) EN 60601-1-2 edition 4 (Medical Devices)
	- Electrostatic Discharge	Air:	EN 61000-4-2, ±15 kV, perf. criteria A
		Contact:	EN 61000-4-2, ±8 kV, perf. criteria A
	- RF Electromagnetic Field		EN 61000-4-3, 3 V/m, perf. criteria A
	- EFT (Burst) / Surge		EN 61000-4-4, ±2 kV, perf. criteria A
		L to L:	EN 61000-4-5, ±1 kV, perf. criteria A
		L to PE:	EN 61000-4-5, ±2 kV, perf. criteria A
	- Conducted RF Disturbances		EN 61000-4-6, 3 Vrms, perf. criteria A
	- PF Magnetic Field	Continuous:	EN 61000-4-8, 30 A/m, perf. criteria A
	- Voltage Dips & Interruptions	230 VAC / 50 Hz:	EN 61000-4-11 30%, 25 periods, perf. criteria A >95%, 0.5 periods, perf. criteria A >95%, 1 period, perf. criteria A >95%, 250 periods, perf. criteria A
		115 VAC / 60 Hz:	EN 61000-4-11 30%, 25 periods, perf. criteria A >95%, 0.5 periods, perf. criteria A >95%, 1 period, perf. criteria A >95%, 250 periods, perf. criteria A
EMC / Environmental	- Certification Documents		www.tracopower.com/overview/tmf30

General Specifications

Relative Humidity			95% max. (non condensing)
Temperature Ranges	- Operating Temperature		–25°C to +70°C
	- Storage Temperature		–40°C to +85°C
Power Derating	- High Temperature		3 %/K above 50°C
	- Low Input Voltage		2 %/V below 100 VAC
		See application note:	www.tracopower.com/overview/tmf30
Cooling System			Natural convection (20 LFM)
Altitude During Operation			5'000 m max.
Switching Frequency			40 - 73 kHz (PWM) 66 kHz typ. (PWM)
Insulation System			Reinforced Insulation
Working Voltage (rated)			250 VAC
Isolation Test Voltage	- Input to Output, 60 s		4'000 VAC
Leakage Current	- Touch Current		100 µA max.
Reliability	- Calculated MTBF		300'000 h (MIL-HDBK-217F, ground benign)
Washing Process			Not allowed
Housing Material			Plastic resin (UL 94 V-0 rated)
Potting Material			Silicone (UL 94 V-0 rated) (Hermetical sealed structure, dust-proof only non water-proof)
Pin Material			Brass
Pin Surface Plating			Tin (120 µm min.), matte
Housing Type			Plastic Case
Mounting Type			PCB Mount
Connection Type			THD (Through-Hole Device)
Soldering Profile			Lead-Free Wave Soldering 270°C / 3 s max.
Weight			135 g

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.


Downloaded from Arrow.com.

Environmental Compliance	- REACH Declaration	www.tracopower.com/info/reach-declaration.pdf
		REACH SVHC list compliant
		REACH Annex XVII compliant
	- RoHS Declaration	www.tracopower.com/info/rohs-declaration.pdf
		Exemptions: 7(c)-I
		(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).)
	- SCIP Reference Number	c7da78a5-a8da-4fd1-9728-ed220668db94

Additional Information

Supporting Documents	www.tracopower.com/overview/tmf30
Frequently Asked Questions	www.tracopower.com/glossary-faq
Glossary	www.tracopower.com/info/glossary.pdf

Outline Dimensions



Pinout	
Pin	**Function**
1	AC (N)
2	AC (L)
3	–Vout
5	+Vout

© Copyright 2025 Traco Electronic AG

Downloaded from Arrow.com.