




CABLE ASSEMBLIES

RF CABLE ASSEMBLIES



✓ Active

TE CONNECTIVITY (TE)

9960 1050 24

Miniature Coax | Coax

1064522-1

TE Internal Number: 1064522-1

Alias ID: 9960-1050-24

EU RoHS Compliant

EU ELV Compliant

Jacket Material FEP Fluorocarbon

Operating Temperature Range -40 – 125 °C [-40 – 257 °F]

Cable Assembly Type Jack-to-Jack Cable Assembly

Connector Impedance (Ω) 50

PRODUCT DRAWING
 English

3D PDF


DOCUMENTATION

Product Drawings

SSMT RIGHT ANGLE JACK TO JACK CABLE ASSEMBLY

PDF **(TIFF AVAILABLE)**

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Assembly Type Jack-to-Jack Cable Assembly

Dielectric Material PTFE Fluorocarbon

Product Type Cable Assembly

Shielded Yes

Configuration Features

Number of Connectorized Ends 2

Electrical Characteristics

Connector Impedance (Ω) 50

Voltage 250 VAC

Insulation Resistance ($M\Omega$) 1000

Signal Characteristics

Frequency (GHz) DC – 6

Body Features

Jacket Material FEP Fluorocarbon

Shield Material Copper Wire

Shield Plating Material Silver

Body Plating Gold

Conductor Plating Silver

Conductor Material Copper Clad Steel

Contact Features

Contact Base Material Beryllium Copper

Contact Mating Area Plating Material Gold

Mechanical Attachment

Mating Diameter (mm) 2.5

Dimensions

Mated Height (mm) 2.1
Conductor Size (AWG) 30

Usage Conditions

Operating Temperature Range -40 – 125 °C [-40 – 257 °F]

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
