




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	25AUG2023	NK	JDB
	E1	DRAWING RE-CREATED IN CREO	23DEC2023	NK	JDB
	E2	REEL CORE DIA CHANGE	24 JUL2024	KA	LET

TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 75 PCS




CONSIDER MOUNTING POSITION; PEG RIGHT



1	-	TAPE AND REEL	6
1	-	HOOD	5
1	-	SOLDER CLIP LEFT	4
1	-	SOLDER CLIP RIGHT	3
4	-	PINS	2
1	-	HOUSING	1
474329-E	REV	DESCRIPTION	ITEM NO.
-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY	PARTS LIST		



V=TURNED CONTACT (PCB SIDE CAN BE USED WITH POTTED COMPOUND)
*=VERSION: WITH HOOD, WITH CUT-IN, Ø8.2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N. K. NIKHIL 25JUL2023	 TE Connectivity						
DIMENSIONS: mm		CHK M. SZELAG 27JUL2023							
	TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mk ISO 8015	APVD J. DE BRUIJN 27JUL2023	NAME M12 MALE, UNI CODE, 4P, 10.5MM SMT, DI V *						
		PRODUCT SPEC 108-94887	-						
		APPLICATION SPEC 114-94781	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
		MATERIAL - -	FINISH -	WEIGHT -	A2	00779	C=474329-E	-	
CUSTOMER DRAWING			SCALE		5:1	SHEET	1 of 1	REV	E2


INSPECTION LEVEL 1: CONTROL CHART REQUIRED
① PROOF OF PROCESS CAPABILITY OR 100% TEST IF
PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
② PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY


③ PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST



PCB-LAYOUT PROPOSAL



PART PACKED WITH HOOD



SCALE 2:1
3D VIEW

1. DRAWING SPECIFICATION ACCORDING TO DOCUMENT
5_3_16-DOC-1806-00915

2. COPLANARITY OF ALL CONTACTS AND CLIPS <= 0.1MM

