



Part Number : [2072350200](#)
Product Description : 824MHz-2170MHz Cellular Flexible Antenna, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Series Number : 207235
Status : Active
Product Category : Antennas



Documents & Resources

Drawings

- [2072350200_sd.pdf](#)
- [2072350100-PK.pdf](#)

3D Models and Design Files

- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [2072350100-AS.pdf](#)
- [2072350100-PS.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Antennas
Series	207235
Description	824MHz-2170MHz Cellular Flexible Antenna, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Name	Cellular Flexible Antenna
Protocol	Cellular
Type	Cellular Antenna, Internal
UPC	191128895934

Electrical

Band#1 F_End (MHz)	960
Band#1 F_Start (MHz)	824
Band#2 F_End (MHz)	2170
Band#2 F_Start (MHz)	1710
Electrical Connectivity	Cable
Peak Gain (dBi)	0.6 @ 824 MHz, 3.6 @ 1710 MHz
Return Loss - S11 (dB)	< -10

Total Efficiency	>40% @ 824 MHz, >60% @ 1710 MHz
------------------	---------------------------------

Physical

Cable Length	200.00mm
Length	40.40mm
Mounting Style	Adhesive
Net Weight	0.805/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	15.40mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
MCRF Jack, Straight, PCB Receptacle, Surface Mount, 1.25mm Mounted Height, 50 Ohms	<u>734120110</u>

This document was generated on Sep 24, 2025