

# SPECIFICATION

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor
- Samsung P/N: **CL05B104KO5NNNO**
- Description : **CAP, 100nF, 16V, ± 10%, X7R, 0402**

## A. Samsung Part Number

CL   05   B   104   K   O   5   N   N   N   O  
 ①   ②   ③   ④   ⑤   ⑥   ⑦   ⑧   ⑨   ⑩   ⑪

|                         |                                       |                   |  |  |  |                          |  |  |  |  |
|-------------------------|---------------------------------------|-------------------|--|--|--|--------------------------|--|--|--|--|
| ① Series                | Samsung Multi-layer Ceramic Capacitor |                   |  |  |  |                          |  |  |  |  |
| ② Size                  | 0402 (inch code)                      | L: 1.00 ±0.05mm   |  |  |  | W: 0.50 ±0.05mm          |  |  |  |  |
| ③ Dielectric            | X7R                                   | ⑧ Inner electrode |  |  |  | Ni                       |  |  |  |  |
| ④ Capacitance           | 100 nF                                | Termination       |  |  |  | Cu                       |  |  |  |  |
| ⑤ Capacitance tolerance | ± 10 %                                | Plating           |  |  |  | Sn 100% (Pb Free)        |  |  |  |  |
| ⑥ Rated Voltage         | 16 V                                  | ⑨ Product         |  |  |  | Normal                   |  |  |  |  |
| ⑦ Thickness             | 0.50 ±0.05mm                          | ⑩ Special         |  |  |  | Reserved for future use  |  |  |  |  |
|                         |                                       | ⑪ Packaging       |  |  |  | Cardboard Type, 10" reel |  |  |  |  |

## B. Samsung Reliability Test and Judgement condition

|                                  | Judgement                                                            | Test condition                                                                   |
|----------------------------------|----------------------------------------------------------------------|----------------------------------------------------------------------------------|
| Capacitance                      | Within specified tolerance                                           | 1kHz±10%      1.0±0.2Vrms                                                        |
| Tan δ (DF)                       | 0.05 max.                                                            |                                                                                  |
| Insulation Resistance            | 10,000Mohm or 100Mohm·μF<br>Whichever is Smaller                     | Rated Voltage      60~120 sec.                                                   |
| Appearance                       | No abnormal exterior appearance                                      | Microscope (×10)                                                                 |
| Withstanding Voltage             | No dielectric breakdown or mechanical breakdown                      | 250% of the rated voltage                                                        |
| Temperature Characteristics      | X7R<br>(From -55℃ to 125℃, Capacitance change should be within ±15%) |                                                                                  |
| Adhesive Strength of Termination | No peeling shall be occur on the terminal electrode                  | 500g·F, for 10±1 sec.                                                            |
| Bending Strength                 | Capacitance change : within ±12.5%                                   | Bending to the limit (1mm) with 1.0mm/sec.                                       |
| Solderability                    | More than 75% of terminal surface is to be soldered newly            | SnAg3.0Cu0.5 solder<br>245±5℃, 3±0.3sec.<br>(preheating : 80~120℃ for 10~30sec.) |
| Resistance to Soldering heat     | Capacitance change : within ±7.5%<br>Tan δ, IR : initial spec.       | Solder pot : 270±5℃, 10±1sec.                                                    |

|                                    | Judgement                                                                                                                       | Test condition                                                                                                                                                    |
|------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Vibration Test</b>              | Capacitance change : within $\pm 5\%$<br>Tan $\delta$ , IR : initial spec.                                                      | Amplitude : 1.5mm<br>From 10Hz to 55Hz (return : 1min.)<br>2hours $\times$ 3 direction (x, y, z)                                                                  |
| <b>Moisture Resistance</b>         | Capacitance change : within $\pm 12.5\%$<br>Tan $\delta$ 0.075 max<br>IR : 500Mohm or 25Mohm . $\mu F$<br>Whichever is Smaller  | With rated voltage<br>40 $\pm 2^\circ C$ , 90~95%RH, 500+12/-0hrs                                                                                                 |
| <b>High Temperature Resistance</b> | Capacitance change : within $\pm 12.5\%$<br>Tan $\delta$ 0.075 max<br>IR : 1000Mohm or 50Mohm . $\mu F$<br>Whichever is Smaller | With 200% of the rated voltage<br>Max. operating temperature<br>1000+48/-0hrs                                                                                     |
| <b>Temperature Cycling</b>         | Capacitance change : within $\pm 7.5\%$<br>Tan $\delta$ , IR : initial spec.                                                    | 1 cycle condition<br>Min. operating temperature $\rightarrow 25^\circ C$<br>$\rightarrow$ Max. operating temperature $\rightarrow 25^\circ C$<br><br>5 cycle test |

### C. Recommended Soldering method :

Reflow ( Reflow Peak Temperature : 260+0/-5 $^\circ C$ , 10sec. Max )

\* For the more detail Specification, Please refer to the Samsung MLCC catalogue.