

Han 10B HTE M32 PFT DL



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 010 1122
Specification	Han 10B HTE M32 PFT DL
HARTING eCatalogue	https://b2b.harting.com/19300101122

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Panel feed through housing
Type	High construction

Version

Locking type	Double locking lever
Han-Easy Lock [®]	Yes
Size	10 B
Version	Top entry
Cable entry	1x M32
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR



Pushing Performance

Material properties

Material (locking)	Polycarbonate (PC) Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate

Specifications and approvals

CE	Yes
----	-----

Commercial data

Packaging size	1
Net weight	325.02 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors