


SERIES: VOF-80B | DESCRIPTION: INTERNAL AC-DC POWER SUPPLY

FEATURES


- universal input range 90~264 Vac
- high efficiency up to 91%
- 2"x3" open frame compact size
- Class I and Class II
- operating altitude 5,000 m
- continuous short circuit protection
- certified to EN/BS EN/UL 62368-1
- certified to IEC/EN 60335-1 (only applies to chassis and board mount models)
- designed to meet EN 55032



MODEL	output voltage		output current	output power	ripple and noise ¹	efficiency ²
	nom (Vdc)	range (Vdc)	max (A)	max (W)	max (mVp-p)	typ (%)
VOF-80B-12	12	11.4~12.6	6.7	80	120	89
VOF-80B-15	15	14.25~15.75	5.36	80	150	89
VOF-80B-24	24	22.8~25.2	3.35	80	240	90
VOF-80B-48	48	45.6~50.4	1.67	80	480	91

Notes: 1. At full load, nominal input, 20 MHz bandwidth oscilloscope, with 10 μ F electrolytic and 0.1 μ F ceramic capacitors on the output.
2. At 230 Vac input and 100% full load at 25°C.

PART NUMBER KEY



INPUT

parameter	conditions/description	min	typ	max	units
voltage ³	AC input	90		264	Vac
	DC input	120		370	Vdc
frequency		50		60	Hz
current	at 100 Vac, full load			1.7	A
inrush current	at 240 Vac, cold start at 25°C			100	A
leakage current				0.25	mA
no load power consumption	48 Vdc output		0.35		W
	all other output models		0.3		W

Note: 3. Safety approvals only apply to the ac input.

OUTPUT

parameter	conditions/description	min	typ	max	units
capacitive load	12 Vdc			13,400	μF
	15 Vdc			11,000	μF
	24 Vdc			6,700	μF
	48 Vdc			3,340	μF
output voltage set point	90 Vac ~ 264 Vac, full load, 25°C	11.88	12	12.12	Vdc
		14.85	15	15.15	Vdc
		23.76	24	24.24	Vdc
		47.52	48	48.48	Vdc
line regulation	90 Vac ~ 264 Vac, full load			±0.5	%
load regulation	10~100% load			±1	%
hold-up time	115 Vac		12		ms
switching frequency	output power = max. rated power		65		kHz

PROTECTIONS

parameter	conditions/description	min	typ	max	units
over voltage protection	built-in TVS component to clamp output voltage				
	12 Vdc			16.2	Vdc
	15 Vdc			18.9	Vdc
	24 Vdc			31.5	Vdc
	48 Vdc			58.8	Vdc
short circuit protection	continuous, auto recovery				

SAFETY & COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to output for 1 minute			3,000	Vac
safety approvals	certified to 62368-1: EN, BS EN, UL certified to 60335-1 ⁴ : IEC, EN designed to meet 55032: EN				
safety class	Class I or Class II				
EMC	EN 55032 Class B, 47 CFR FCC Part 15 Subpart B, Oct.2014 EN 61000-3-2:2019, EN 61000-3-3:2013+A1:2019, EN 61000-6-3:2021, EN 61000-6-4:2019, EN 61204-3:2018, Class B				
conducted emissions	EN 55032, EN 61204-3:2018, EN 61000-6-3:2021, EN 61000-6-4:2019, Class B, 47 CFR FCC Part 15 Subpart B, Class B				
radiated emissions	EN 55032, EN 61204-3:2018, EN 61000-6-3:2021, EN 61000-6-4:2019, Class B, 47 CFR FCC Part 15 Subpart B, Class B				
harmonic current emissions	EN 61000-3-2:2019				
voltage fluctuations & flicker	EN 61000-3-3:2013+A1:2019				
EMI	EN 55035, EN 61204-3:2018, EN 61000-6-1:2019, EN 61000-6-2:2019				

SAFETY & COMPLIANCE

parameter	conditions/description	min	typ	max	units
ESD	IEC 61000-4-2:2008, air discharge: ±8kV, contact discharge: ±4kV, perf. Criteria A				
radiated immunity	IEC 61000-4-3:2020, perf. Criteria A				
EFT/burst	IEC61000-4-4:2012, ±1kV, ±2kV, perf. Criteria A				
surge	IEC 61000-4-5:2014+A1:2017, L-N: ±0.5kV, ±1kV, L-E (ground): ±0.5kV, ±1kV, ±2kV, perf. Criteria A				
conducted immunity	IEC 61000-4-6:2013+COR1:2015				
PFMF	IEC 61000-4-8:2009, perf. Criteria A				
voltage dips and interruption	IEC 61000-4-11:2020, Dip: 30% reduction, Dip >95% Reduction, perf. Criteria A IEC 61000-4-11:2020, >95% reduction, perf. Criteria B				
vibration	meet MIL-STD-810F table 514.5C-VIII,15~2000Hz, X,Y,Z axis, 1 hour (each axis). total 3 hrs		4		g
shock	meet MIL-STD-810F table 516.5, table 516.5-I 10ms, each axis 3 times (±X,±Y,±Z axis)		75		g
MTBF	as per MIL-HDBK-217F at 25°C as per Telcordia SR-322 at 25°C	410,000 3,100,000			hours hours
RoHS	yes				

Note: 4. Safety approvals only apply to the chassis mount and board mount models.


ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
operating temperature	see derating curve	-30		80	°C
storage temperature		-30		85	°C
storage humidity	non-condensing			93	%
altitude				5,000	m

MECHANICAL



parameter	conditions/description	min	typ	max	units
dimensions	chassis mount: 76.20 x 50.80 x 34.00 [3.000 x 2.000 x 1.339 inch] board mount: 76.20 x 50.80 x 35.90 [3.000 x 2.000 x 1.413 inch] covered: 81.28 x 62.00 x 40.00 [3.200 x 2.441 x 1.575 inch]				mm mm mm
weight	chassis mount board mount covered		135 133 174		g g g

DERATING CURVE





DERATING CURVE (CONTINUED)

POWER DERATING CURVE
(natural convection)





POWER DERATING CURVE
(natural convection)





EFFICIENCY CURVES



EFFICIENCY VS INPUT LOAD
VOF-80B-12





EFFICIENCY VS INPUT LOAD
VOF-80B-15



EFFICIENCY VS INPUT LOAD
VOF-80B-24



EFFICIENCY VS INPUT LOAD
VOF-80B-48




MECHANICAL DRAWING

Chassis mount

units: inches [mm]
tolerance inches: x.xx=±0.03, x.xxx=±0.020
mm: x.x=±0.7, x.xx=±0.50

AC Input Connector (CN1) TKP PVHI-03N2 or equivalent			
PIN	Function	Mating Housing	Terminal
1	AC(N)	JST VHR-3N or equivalent	JST SVH-21T-P1.1 or equivalent
2	-		
3	AC(L)		



DC Output Connector (CN2): TKP PVHI-04 or equivalent			
PIN	Function	Mating Housing	Terminal
1	-Vout	JST VHR-4N or equivalent	JST SVH-21T-P1.1 or equivalent
2	-Vout		
3	+Vout		
4	+Vout		



Board mount

units: inches [mm]
tolerance inches: x.xx=±0.03, x.xxx=±0.020
mm: x.x=±0.7, x.xx=±0.50

PIN CONNECTIONS	
PIN	Function
1	AC(N)
2	AC(L)
3	-Vout
4	-Vout
5	+Vout
6	+Vout






MECHANICAL DRAWING (CONTINUED)

Covered

units: inches [mm]
tolerance inches: x.xx=±0.03, x.xxx=±0.020
mm: x.x=±0.7, x.xx=±0.50

AC Input Connector (CN1) TKP PVHI-03N2 or equivalent			
PIN	Function	Mating Housing	Terminal
1	AC(N)	JST VHR-3N or equivalent	JST SVH-21T-P1.1 or equivalent
2	-		
3	AC(L)		

DC Output Connector (CN2): TKP PVHI-04 or equivalent			
PIN	Function	Mating Housing	Terminal
1	-Vout	JST VHR-4N or equivalent	JST SVH-21T-P1.1 or equivalent
2	-Vout		
3	+Vout		
4	+Vout		



REVISION HISTORY

rev.	description	date
1.0	initial release	10/19/2023
1.01	safeties, mechanical drawing & MTBF updated	04/10/2026

The revision history provided is for informational purposes only and is believed to be accurate.



15575 SW Sequoia Pkwy #100
Portland, OR 97224
800.275.4899

Fax 503.612.2383
Belfuse.com
powersupport@belf.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.