




+ CONNECTORS

MULTIPLE CONFIGURATION PCB HEADERS & RECEPTACLES



✓ Active

TE CONNECTIVITY (TE)  
13P MOD2 STIFT LEI  
AMPMODU | AMPMODU Headers

1-826942-3  
TE Internal Number: 1-826942-3

EU RoHS Compliant  
EU ELV Compliant

Number of Positions 26  
Centerline (Pitch) 2.54 mm [ .1 in ]  
Connector & Contact Terminates To Printed Circuit Board  
Connector Style Plug  
Header Type Breakaway

↓ PRODUCT DRAWING  
English

DOCUMENTATION

Product Drawings

AMPMODU II STIFTELEISTE ZWEIREIHIG  
PDF  
English

Agency Approvals

Agency Approval Document

AMPMODU CONNECTOR REPORT (GERMANY)  
PDF  
English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Connector & Contact Terminates To** Printed Circuit Board
- Connector Style** Plug
- Header Type** Breakaway
- PCB Mounting Orientation** Vertical
- Connector Type** Header
- Row-to-Row Spacing** 2.54 mm [ .1 in ]
- Gasket** Without
- Profile** Standard
- Product Type** Connector
- Stabilizers** Without
- Board Standoff** Without
- Strain Relief** Without

Configuration Features

- Selectively Loaded** No
- Number of Positions** 26
- Number of Rows** 2
- Keyed** No

Electrical Characteristics

- Dielectric Withstanding Voltage** 1000 V

Body Features

- Post Size** .63 mm [ .024 in ]

Contact Features

- Solder Tail Contact Plating Material** Tin
- Contact Protection** Without
- Contact Shape** Square
- Contact Current Rating (Max) (A)** 5
- Contact Base Material** Phosphor Bronze
- Contact Mating Area Plating Thickness (µm)** 2
- Contact Type** Pin
- Contact Mating Area Plating Material** Tin

Termination Features

- Termination Method to PC Board** Through Hole
- Termination Post Length** 3.2 mm [ .1259 in ]
- Termination End Plating Material** Tin
- Termination End Plating Thickness (µm)** 2

Mechanical Attachment

- Panel Mount Retention** Without
- Mating Connector Lock** Without
- PCB Mounting Style** Through Hole
- PCB Mount Retention** Without
- Mating Alignment** Without

Housing Features

**Centerline (Pitch)** 2.54 mm [ .1 in ]  
**Housing Material** PBT GV  
**Housing Color** Green

Dimensions

**Mating Post Length** 5.8 mm [ .228 in ]

Usage Conditions

**Operating Temperature Range (°C)** -65 – 105  
**High Temperature Housing** No

Operation/Application

**High Speed Serial Data Connector** No

Industry Standards

**UL Flammability Rating** UL 94V-0

Packaging Features

**Packaging Quantity** 250  
**Packaging Method** Box

PRODUCT COMPLIANCE



Statement of Compliance

**Statement of Compliance**  
PDF