


SPECIFICATION CONTROL DRAWING		55PC6000	
TITLE	TWO CONDUCTOR CABLE, DOUBLE SHIELDED, DOUBLE JACKETED, GENERAL PURPOSE, 600 VOLT	Date 5-15-13	Revision E
This specification sheet forms a part of the latest issue of Raychem Specification 55PC.			



CABLE CONSTRUCTION DETAILS												
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	1 st SHIELD SIZE (AWG)	1 st JACKET THICKNESS (in.)		2 nd SHIELD SIZE (AWG)	2 nd JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
			LOWER SPEC LIMIT	TARGET WALL		LOWER SPEC LIMIT	TARGET WALL	LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC6000-24-*	24	38	.0050	.0065	38	.0055	.0070	.136	.141	.147	16.70	17.35
55PC6000-22-*	22	38	.0055	.0070	38	.0055	.0070	.148	.154	.160	20.12	20.84
55PC6000-20-*	20	38	.0055	.0070	38	.0060	.0075	.166	.172	.178	25.22	26.01
55PC6000-18-*	18	38	.0055	.0070	38	.0060	.0075	.185	.191	.197	31.89	32.82
55PC6000-16-*	16	38	.0060	.0075	38	.0060	.0075	.201	.207	.213	37.45	38.46
55PC6000-14-*	14	38	.0060	.0075	38	.0060	.0080	.232	.238	.245	50.30	51.48
55PC6000-12-*	12	38	.0060	.0080	38	.0065	.0085	.271	.278	.285	69.20	70.68

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.			
1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.			
Page 1 of 2	Raychem, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks.		 Raychem Wire & Cable 501 Oaks Avenue Redwood City, CA 94063-3800 Phone: 1-800-227-8816 Fax: 1-650-361-6297
	DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.		
	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.		

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour

DIELECTRIC WITHSTAND:

1500 volts (rms), 60 Hz conductor to conductor and shield

500 volts (rms), 60 Hz shield to shield

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum) (each)

Tensile Strength, 5000 lbf/in² (minimum) (each)

JACKET FLAWS:

Spark Test, 1000 volts (rms)

Impulse Dielectric Test, 6.0 kV (peak)

SHIELD COVERAGE:

85% (minimum) (each)

VOLTAGE WITHSTAND (Post Environmental):

1000 volts (rms), 60 Hz, 1 minute

CABLE IDENTIFICATION: Mark outer jacket surface in a contrasting color at 12 inch (nominal) intervals as follows: " 55PC6000-AWG ** "

** = Applicable Manufacturer CAGE code as follows:

06090 = Menlo Park, CA

SU473 = Tijuana, MX

PART NUMBER:

The "*" in the part numbers on page 1 shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the inner jacket color and a dash separating the inner jacket color from the outer jacket color.

1/ Example: AWG 22, red and blue component wires; white inner jacket and white outer jacket:
55PC6000-22-2/6-9-9

1/ See footer section on page 1