



Part Number : [1300108033](#)

Product Description : Mini-Change Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 16 AWG, Gray PUR Cable, 10.0m (32.81') Length, Zinc Die-Cast Coupling Nut

Series Number : 130010

Status : Obsolete

Product Category : Circular Industrial Cordsets

Engineering Part Number : 115030B21M100

Documents and Resources

Drawings

[1300108033_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Obsolete
Category	Circular Industrial Cordsets
Series	130010
Description	Mini-Change Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 16 AWG, Gray PUR Cable, 10.0m (32.81') Length, Zinc Die-Cast Coupling Nut
IP Rating	IP67
Product Name	Mini-Change
Protocol	DeviceNet
Type	Double Ended
UPC	887191260778

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V AC/DC

Physical

Cable Diameter	12.70mm (.500")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Gray
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	PUR

Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	UL 20233
Wire Size (AWG)	16

This document was generated on Apr 09, 2026

Obsolete