





features

- Superior to RK73B/RK73H series in surge withstanding voltage and high power
- Resistance tolerance is available from $\pm 0.5\%$
- Suitable for both reflow and flow solderings
- Products with lead-free terminations meet EU RoHS requirements. EU RoHS regulation is not intended for Pb-glass contained in electrode, resistor element and glass.
- AEC-Q200 Qualified

dimensions and construction



Type (Inch Size Code)	Dimensions inches (mm)				
	L	W	c	d	t
SG73S1E (0402)	.039 ^{+0.004} _{-.002} (1.0 ^{+0.1} _{-0.05})	.02±.002 (0.5±0.05)	.006±.004 (0.15±0.1)	.010 ^{+0.002} _{-.004} (0.25 ^{+0.05} _{-0.1})	.014±.002 (0.35±0.05)
SG73S1J (0603)	.063±.008 (1.6±0.2)	.031±.004 (0.8±0.1)	.012±.004 (0.3±0.1)	.012±.004 (0.3±0.1)	.018±.004 (0.45±0.1)
SG73S1J AT (0603)			.014±.006 (0.35±0.15)	.02±.008 (0.5±0.2)	
SG73S2A (0805)	.079±.008 (2.0±0.2)	.049±.004 (1.25±0.1)	.012 ^{+0.008} _{-.004} (0.3 ^{+0.2} _{-0.1})	.012 ^{+0.008} _{-.004} (0.3 ^{+0.2} _{-0.1})	.02±.004 (0.5±0.1)
SG73S2A AT (0805)			.018±.010 (0.45±0.25)	.024±.008 (0.6±0.2)	.022±.004 (0.55±0.1)
SG73S2B (1206)		.063±.008 (1.6±0.2)	.016 ^{+0.008} _{-.004} (0.4 ^{+0.2} _{-0.1})	.016 ^{+0.008} _{-.004} (0.4 ^{+0.2} _{-0.1})	
SG73S2B AT (1206)	.126±.008 (3.2±0.2)		.022±.014 (0.55±0.35)	.031±.008 (0.8±0.2)	.024±.004 (0.6±0.1)
SG73S2E (1210)		.102±.008 (2.6±0.2)	.016 ^{+0.008} _{-.004} (0.4 ^{+0.2} _{-0.1})	.016 ^{+0.008} _{-.004} (0.4 ^{+0.2} _{-0.1})	

ordering information

SG73S	2B		T	TD	1001	F
Type	Size	Characteristic	Termination Material	Packaging	Nominal Resistance	Tolerance
SG73S	1E 1J 2A 2B 2E	Nil: Standard A: Heat shock resistance *	T: Sn	TP: 0402, 0603, 0805: 2mm pitch punch paper TD: 0603, 0805, 1206, 1210: 4mm pitch punched paper TE: 0805, 1206, 1210: 4mm embossed plastic	±0.5%, ±1%: 3 significant figures + 1 multiplier "R" indicates decimal on value <100Ω ±2%, ±5%: 2 significant figures + 1 multiplier "R" indicates decimal on value <10Ω	D: ±0.5% F: ±1% G: ±2% J: ±5%

* 1J, 2A, and 2B are available for heat shock resistance.

Contact us when you have control request for environmental hazardous material other than the substance specified by EU RoHS.

For further information on packaging, please refer to Appendix A

**anti-surge endured surge voltage
thick film chip resistor**
applications and ratings

Part Designation	Power Rating ^{*1}	Rated Ambient Temp.	Rated Terminal Part Temp.	T.C.R. (ppm/°C) Max.	Resistance Range (Ω)			Maximum Working Voltage	Maximum Overload Voltage	Operating Temp. Range
					(E-24)/E-96 (D±0.5%)	(E-24)/E-96 (F±1%)	(E-24) (G±2%, J±5%)			
SG73S1E (0402)	0.33W	70°C	105°C	±200	10 - 1M	1 - 1M	1 - 10M	75V	100V	-55°C to +155°C
SG73S1J (0603)	0.5W	70°C	105°C	±100	510 - 576k	510 - 576k	510 - 560k	150V	200V	
				±100* ²	10 - 499 590k - 1M	1 - 499 590k - 1M	1 - 470 620k - 10M			
SG73S2A (0805)	0.75W	70°C	105°C	±200	10 - 1M	1 - 1M	1 - 10M	400V	600V (800V)* ³	
SG73S2B (1206)	1W	70°C	105°C	±200	10 - 1M	1 - 1M	1 - 10M	200V	400V	
SG73S2E (1210)	1.5W	70°C	105°C	±200	10 - 1M	1 - 1M	1 - 10M	200V	400V	

^{*1} If the terminal part temperature exceeds the rated part temperature, even if it is below the rated ambient temperature, apply the derating curve for the terminal part temperature.


^{*2} Cold T.C.R. (-55°C ~ +25°C) is +150 x 10⁻⁶/K

^{*3} Applies when power rating is 0.4W or lower.


Rated voltage = $\sqrt{\text{Power rating} \times \text{resistance value}}$ or max. working voltage, whichever is lower

Please contact KOA Speer for how to handle a specific surge/pulse

If any questions should arise whether to use the "Rated Ambient Temperature" or the "Rated Terminal Part Temperature," please give priority to the "Rated Terminal Part Temperature."

environmental applications
Derating Curve


For resistors operated at an ambient temperature of 70°C or above, the power rating shall be derated in accordance with the derating curve.



For resistors operated at a terminal part temperature of 105°C or above, the power rating shall be derated in accordance with the derating curve.

For more details on derating click here ["Derating Curves – Caution & Terms."](#)

Additional environmental applications can also be found at www.koaspeer.com






Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

04/15/26



anti-surge endured surge voltage thick film chip resistor

environmental applications (continued)


ESD Limiting Voltage



Temperature Rise



Regarding the temperature rise, the value of the temperature varies per conditions and board for use since the temperature is measured under our measuring conditions.



Performance Characteristics

Parameter	Requirement Δ R ±(%+0.1Ω)		Test Method					
	Limit	Typical						
Resistance	Within specified tolerance	—	25°C					
T.C.R.	Within specified T.C.R.	—	+25°C/-55°C and +25°C/+125°C					
Overload (Short time)	±2%	±0.5%	Type	1E	1J	2A	2B	2E
			Overload	1.25W	2.063W	2W (1.6W ³)	3W	4W
Resistance to Solder Heat	±1%	±0.75%	260°C ± 5°C, 10 seconds ± 1 second					
Rapid Change of Temperature	±0.5%: Characteristic (Nil) Standard ±1%: Characteristic (A) Heat Shock Resistance	±0.3%: Characteristic (Nil) Standard ±0.5%: Characteristic (A) Heat Shock Resistance	Characteristic (Nil) Standard: -55°C (30 min.)/+125°C (30 min.) 100 cycles Characteristic (A) Heat Shock Resistance: -55°C (30 min.)/+125°C (30 min.) 1000 cycles					
Moisture Resistance	±3%	±0.75%	40°C ± 2°C, 90%~95%RH, 1000 hours; 1.5 hr ON, 0.5 hr OFF cycle					
Endurance at 70°C or Rated Terminal Part Temperature	±3%	±0.75%	70°C ± 2°C or rated terminal part temp. ± 2°C 1000 hours; 1.5 hr ON, 0.5 hr OFF cycle					
High Temperature Exposure	±1%	±0.3%	+155°C, 1000 hours					

Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

04/16/26