



© 2020 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F1	ECR-20-009991	16JUL2020	EO	RN
	F2	ECR-22-141885	09JUN2022	RK	JM











NOTE:
Bemerkung:

SOLDER-CONTACT: 88997; 487992; 487136; 487137
SOLDER-Kontakt: 88997; 487992; 487136; 487137

VIEW POSITION 112 DOES NOT MATCH THE ORIGINAL
SEE DRAWING 1-879103-1
Ansicht Position 112 nicht detailgetreu
Siehe Zeichnung 1-879103-1

FFC APPLICATOR TEST REPORT:
FFC APPLICATOR ACCEPTANCE ACCORDING TO
FFC_APPLICATOR_TEST_REPORT


LINK:https://doclink.connect.te.com/Thingworx/Runtime/index.html#mashup=DSD.DeliverableRetrieval.Mashup&deliverableId=00000000000031C7629112000006905A&forceDownload=true

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17AUG2011 B. Muth/ A. Roehnisch	TE Connectivity
		CHK 17AUG2011 T. Weissgerber	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	APVD 17AUG2011 T. Weissgerber	NAME FFC APPLICATOR, SOLDER TAB 100 FFC Applikator, Loetkontakt 100
		PRODUCT SPEC -	
		APPLICATION SPEC 114-16015	SIZE A1 · CAGE CODE 00779 · DRAWING NO C-5-528441-7 · RESTRICTED TO -
MATERIAL - -	FINISH - -	WEIGHT 4,200 kg	CUSTOMER DRAWING · SCALE 1:1 · SHEET 1 OF 7 · REV F2

Downloaded from Arrow.com.

© 2020 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL –
–

FINISH –
–

DWN 17AUG2011 B. Muth/ A. Roehnisch
CHK 17AUG2011 T. Weissgerber
APVD 17AUG2011 T. Weissgerber
PRODUCT SPEC –
APPLICATION SPEC SEE SHEET 1
WEIGHT SHEET 1

TE Connectivity

NAME
FFC APPLICATOR, SOLDER TAB 100
FFC Applikator, Loetkontakt 100


SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-5-528441-7	–

CUSTOMER DRAWING | SCALE | SHEET 2 OF 7 | REV F2

Downloaded from Arrow.com.

© 2020TE Connectivity. All Rights Reserved. . a TE Connectivity Ltd. company. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1	SEE SHEET 1		





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17AUG2011 B. Muth/ A. Roehnisch	TE Connectivity
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-	CHK 17AUG2011 T. Weissgerber	NAME FFC APPLICATOR, SOLDER TAB 100 FFC Applikator, Loetkontakt 100
		APVD 17AUG2011 T. Weissgerber	
		PRODUCT SPEC -	
		APPLICATION SPEC SEE SHEET 1	SIZE A3 / CAGE CODE 00779 / DRAWING NO C-5-528441-7 / RESTRICTED TO -
MATERIAL - -	FINISH - -	WEIGHT SHEET 1	CUSTOMER DRAWING / SCALE / SHEET 3 OF 7 / REV F2

Downloaded from Arrow.com.

© 2020TE Connectivity. All Rights Reserved. . a TE Connectivity Ltd. company. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1	SEE SHEET 1		





THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL: -

FINISH: -

DWN: B. Muth/ A. Roehnisch 17AUG2011
CHK: T. Weissgerber 17AUG2011
APVD: T. Weissgerber 17AUG2011
PRODUCT SPEC: -
APPLICATION SPEC: SEE SHEET 1
WEIGHT: SHEET 1

TE Connectivity

NAME: FFC APPLICATOR, SOLDER TAB 100
FFC Applikator, Loetkontakt 100

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-5-528441-7	-

CUSTOMER DRAWING | SCALE | SHEET 4 OF 7 | REV F2

1470-19 (3/13)

Downloaded from Arrow.com.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

POS	QTY	TE P/N	DESCRIPTION	S=Spare Parts W=Wear Parts	S	W
30	1	2-523724-8	CRIMPER SET		X	X
29	1	2-523724-7	MOVABLE PUNCH		X	
28	1	2-523724-6	PUNCH SUPPORT		X	
27	1	2-523724-5	COVER PUNCH		X	
25	1	1-523725-9	GUIDE		X	
24	2	523724-3	SCREW M3x6		X	
23	1	2-523724-2	PLATE		X	
22	1	523724-2	SCREW M5x45		X	
21	1	3-523725-5	GUIDE		X	
20	2	2-523724-0	SCREW M5x10		X	
19	2	1-523724-9	SCREW M6x16		X	
18	1	1-523724-8	PLATE BASE		X	
17	1	523725-5	FRONT GUIDE		X	
16	1	1-523724-6	GUIDE PLATE SUPPORT		X	
15	1	3-523725-4	REAR GUIDE		X	
14	1	1-523724-4	ADJUSTMENT BLOCK		X	
13	1	1-523793-4	NUT M5		X	
12	1	1-523724-2	CLUTCH SPACER		X	
11	1	1-523724-1	CLUTCH SPRING		X	
10	1	4-523725-2	TERMINAL CLUTCH, PLASTIC		X	
9	1	523724-9	PIN D. 3x25		X	
8	1	523724-8	CLUTCH LEVER		X	
7	1	523724-7	FEED ROLLER		X	
6	1	523724-6	CLUTCH SUPPORT		X	
5	1	523724-5	COUNTER		X	
4	1	1-523793-3	COUNTER COVER		X	
3	2	523724-3	SCREW M3x6		X	
2	6	523724-2	SCREW M5x45		X	
1	1	523724-1	FRAME		X	

© 2020 TE Connectivity. All Rights Reserved.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

DWN B. Muth/ A. Roehnisch 17AUG2011
CHK T. Weissgerber 17AUG2011
APVD T. Weissgerber 17AUG2011
PRODUCT SPEC -
APPLICATION SPEC SEE SHEET 1
WEIGHT SHEET 1

MATERIAL -
FINISH -

TE Connectivity

NAME FFC APPLICATOR, SOLDER TAB 100
FFC Applikator, Loetkontakt 100

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A4	00779	C-5-528441-7	-

CUSTOMER DRAWING | SCALE 1:1 | SHEET 5 OF 7 | REV F2

Downloaded from Arrow.com.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

68	1	6-523724-6	LEVER	X	
67	1	6-523724-5	FRONT DIE CUT OFF	X	X
66	1	9-523724-9	RAM	X	
65	1	6-523724-3	SCREW M6X6	X	
64	1	6-523724-2	BRASS RING	X	
63	1	6-523724-1	MAGNET	X	
62	1	6-523724-0	SPACER	X	
61	1	5-523724-9	CAMME DISC	X	
60	1	5-523724-8	WIRE ADJUSTMENT DISC	X	
59	1	5-523724-7	RAM	X	
58	1	5-523724-6	PIN 5X12	X	
57	1	5-523724-5	FEED EQUALIZER	X	
56	1	5-523724-4	SPRING FINGER	X	
55	1	5-523724-3	FEED LEVER	X	
54	1	5-523724-2	FEED ADJUSTMENT SCREW	X	
53	1	5-523724-1	FEED SMALL BLOCK	X	
52	1	5-523724-0	BRACKET	X	
51	2	4-523724-9	SCREW M4X20	X	
50	1	4-523724-8	SPRING FEED	X	
49	1	4-523724-7	PIN	X	
48	1	4-523724-6	CENTER SUPPORT	X	
47	1	4-523724-5	PIN FOR LEVER FEED	X	
45	1	1-523793-2	CENTER CONTACT	X	
44	1	4-523724-2	THREADED BUSH	X	
42	1	4-523724-0	SPACER FOR 868987; 1452128	X	
40	1	3-523724-8	SCREW M4X30	X	
39	1	3-523724-7	NUT M4	X	
38	1	3-523724-6	FEEDING COVER	X	
37	1	3-523724-5	BELLEVILLE WASHER	X	
36	1	3-523724-4	NUT M12	X	
35	1	3-523724-3	SCREW M6X20	X	
34	2	3-523724-2	SCREW M5X12	X	
33	1	3-523724-1	COVER	X	
32	1	3-523724-0	SPRING DIE CUT OFF	X	
31	1	3-523725-3	BLOCK DIE CUT OFF	X	X

© 2020 TE Connectivity. All Rights Reserved.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

DWN 11AUG2011 B. Muth/ A. Roehnisch
CHK 11AUG2011 T. Weissgerber
APVD 11AUG2011 T. Weissgerber
PRODUCT SPEC -
APPLICATION SPEC SEE SHEET 1
WEIGHT SHEET 1

MATERIAL -
FINISH -

TE Connectivity

NAME FFC APPLICATOR, SOLDER TAB 100
FFC Applikator, Loetkontakt 100

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A4	00779	C-5-528441-7	-

CUSTOMER DRAWING | SCALE 1:1 | SHEET 6 OF 7 | REV F2

Downloaded from Arrow.com.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

112	1	1-879103-1	DISC ADJUSTABLE -F	X	
111	2	2168078-1	SCREW, DRIVE, ROUND HD, METALLIC	X	
110	1	9-519637-1	PLATE, IDENTIFICATION	X	
109	1	3-523793-7	COUNTER SPACER	X	
108	2	2-523793-7	PIN D.3X6	X	
107	1	1-523793-4	NUT M5	X	
106	1	1-523725-5	SPECIAL SCREW M5X30	X	
105	1	2-523793-6	SCREW M3X5	X	
104	1	2-523793-5	SUPPORT CONTACT SCREW	X	
103	2	2-523793-4	GUIDE SCREW	X	
102	1	2-523793-3	SPRING	X	
101	2	2-523793-2	SPRING	X	
100	1	2-523793-1	PIN	X	
99	1	2-523793-0	LEVER	X	
98	1	1-523793-9	SLIDE PLATE	X	
97	1	1-523793-8	GUIDE SUPPORT	X	
96	1	1-523793-7	GUIDE	X	
95	1	3-523725-6	CONTACT SUPPORT	X	
94	1	3-519627-0	FFC-ANVIL	X	X
90	2	8-523724-4	SPRING CAMME	X	
89	2	8-523724-3	SCREW M4X10	X	
88	2	8-523724-2	BALL	X	
87	1	8-523724-1	FEED CAMME	X	
86	1	8-523724-0	SCREW M4x8	X	
81	1	7-523724-9	SPRING SCREW	X	
80	1	7-523724-8	NUT	X	
79	1	7-523724-7	SPRING FINGER	X	
78	1	7-523724-6	PIN D. 2x20	X	
77	1	7-523724-5	WASHER	X	
76	1	7-523724-4	STEP BEARING	X	
75	1	7-523724-3	PIN	X	
74	2	7-523724-2	PIN	X	
73	1	7-523724-1	FEED LEVER	X	
72	1	7-523724-0	REAR SUPPORT	X	
71	1	6-523724-9	LEVER	X	
70	1	6-523724-8	FINGER SUPPORT	X	
69	1	6-523724-7	FEEDING FINGER	X	X

© 2020 TE Connectivity. All Rights Reserved.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

DWN 17AUG2011 B. Muth/ A. Roehnisch
CHK 17AUG2011 T. Weissgerber
APVD 17AUG2011 T. Weissgerber
PRODUCT SPEC -
APPLICATION SPEC SEE SHEET 1
WEIGHT SHEET 1

MATERIAL -
FINISH -

TE Connectivity

NAME FFC APPLICATOR, SOLDER TAB 100
FFC Applikator, Loetkontakt 100

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A4	00779	C-5-528441-7	-

CUSTOMER DRAWING | SCALE 1:1 | SHEET 7 OF 7 | REV F2

1469-35 (3/13)

Downloaded from Arrow.com.