

har-button latching function



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 453 1104
Specification	har-button latching function
HARTING eCatalogue	https://b2b.harting.com/09454531104

Identification

Category	Operator Interfaces
Series	har-button
Element	Push button
Specification	with latching function

Version

Diameter of the mounting hole	22.3 mm
Details	This item requires additional contact blocks, a module holder, and a protective cap. Please select these under "Matching Products".

Technical characteristics

Actuation path	6 mm
Overvoltage category	III (protection by low voltage)
Tightening torque	1.5 ... 2.2 Nm Fixing nut
Operating temperature	-25 ... +70 °C
Storage temperature	-40 ... +80 °C
Degree of protection acc. to IEC 60529	IP65 / IP67
Isolation group	I (600 ≤ CTI)
Thickness of the panel	1 ... 7 mm

Material properties

Colour	anthracite
--------	------------



Pushing Performance
Since 1945

Specifications and approvals

Specifications	EN 60947-5-1
----------------	--------------

Commercial data

Packaging size	10
Net weight	14.5 g
Country of origin	Germany
European customs tariff number	85365080
ETIM	EC000221